



Pushing Performance
Since 1945

Han 24HPR-HTE4-HC-SCL-M32/M32/M32/M10



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 024 0459
Specification	Han 24HPR-HTE4-HC-SCL-M32/M32/ M32/M10
HARTING eCatalogue	https://harting.com/19400240459

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Hood
Description of hood/housing	High construction

Version

Size	24 B
Version	Top entry
Number of cable entries	4
Cable entry	1x M10 3x M32
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments

Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	798 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140356252
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19400240459](#)