



Pushing Performance  
Since 1945

# HARAX M8-S male 4-pole



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 21 02 151 1405  |
| Specification      | HARAX M8-S male 4-pole  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/21021511405">https://b2b.harting.com/21021511405</a> |

## Identification

|                |                        |
|----------------|------------------------|
| Category       | Connectors             |
| Series         | Circular connectors M8 |
| Identification | M8-S                   |
| Element        | Cable connector        |
| Specification  | Straight               |

## Version

|                    |                              |
|--------------------|------------------------------|
| Termination method | HARAX® connection technology |
| Gender             | Male                         |
| Shielding          | Unshielded                   |
| Number of contacts | 4                            |
| Coding             | A-coding                     |
| Locking type       | Screw locking                |

## Technical characteristics

|                         |                   |
|-------------------------|-------------------|
| Conductor cross-section | 0.14 ... 0.34 mm² |
| Conductor cross-section | AWG 26 ... AWG 22 |
| Wire outer diameter     | ≤1.6 mm           |
| Rated current           | 4 A               |
| Rated voltage           | 32 V              |
| Rated impulse voltage   | 1.5 kV            |
| Pollution degree        | 3                 |
| Overvoltage category    | III               |



**Pushing Performance**  
Since 1945

## Technical characteristics

|   |                             |
|---|-----------------------------|
| Insulation resistance                     | $>10^8 \Omega$              |
| Contact resistance                        | $\leq 10 \text{ m}\Omega$   |
| Tightening torque                         | 0.4 Nm                      |
| Wrench size (knurled screw / knurled nut) | 9                           |
| Limiting temperature                      | -40 ... +85 °C              |
| Mating cycles                             | $\geq 100$                  |
| Degree of protection acc. to IEC 60529    | IP67 locked condition       |
| Cable diameter                            | 2.5 ... 5.1 mm              |
| Isolation group                           | I ( $600 \leq \text{CTI}$ ) |

## Material properties

|                                      |  |
|--------------------------------------|--|
| Material (insert)                    | Polyamide (PA)   |
| Material (contacts)                  | Copper alloy   |
| Surface (contacts)                   | Au over Ni Mating side                                 |
| Material (hood/housing)              | Polyamide (PA)<br>Zinc die-cast                        |
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50   |
| REACH Annex XVII substances          | Not contained  |
| REACH ANNEX XIV substances           | Not contained  |
| REACH SVHC substances                | Yes  |
| REACH SVHC substances                | Lead   |
| ECHA SCIP number                     | 0d7d3693-d625-47ab-934a-d241bf72c86e                   |
| California Proposition 65 substances | Yes  |
| California Proposition 65 substances | Lead<br>Nickel   |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08)                                   |
| Requirement set with Hazard Levels   | R26  |

## Specifications and approvals

|                |                 |
|----------------|-----------------|
| Specifications | IEC 61076-2-104 |
|----------------|-----------------|



Pushing Performance  
Since 1945

Specifications and approvals

|          |                                   |
|----------|-----------------------------------|
| UL / CSA | UL 1977 ECBT2.E102079             |
|          | CSA-C22.2 No. 182.3 ECBT8.E102079 |

Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 11.5 g   |
| Country of origin              | Germany  |
| European customs tariff number | 85366990   |
| GTIN                           | 5713140136939                                    |
| ETIM                           | EC002635   |
| eCl@ss                         | 27440116 Circular connector (for field assembly) |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21021511405](#)