



Pushing Performance  
Since 1945

# Ha-Vis EtherRail 4x2xAWG24/7 CAT7 10m




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 600 0694
Specification	Ha-Vis EtherRail 4x2xAWG24/7 CAT7 10m
HARTING eCatalogue	<a href="https://b2b.harting.com/09456000694">https://b2b.harting.com/09456000694</a>

## Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (round)
Description of the cable	for railway applications

## Version

Cable length	10 m
Number of cores	8
Core structure	4x 2x AWG 24/7

## Technical characteristics

Transmission characteristics	Cat. 7 Class F up to 600 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +80 °C unmoved
	-25 ... +70 °C moved
Cable diameter	8.1 mm ± 0.3 mm
Minimum bending radius	6x Cable diameter
Test voltage U <sub>r.m.s.</sub>	1 kV Wire / wire / shielding
Coupling attenuation @ 20 °C / 10 MHz	5 mΩ/m



**Pushing Performance**  
Since 1945

## Technical characteristics

Conductor resistance @ 20 °C	≤84 Ω/km
Insulation resistance @ 20 °C	≥5,000 MΩ x km
Signal run time @ 20 °C	≤4.4 ns/m
Impedance @ 100 MHz	100 Ω ±5 %

## Material properties

Material (cable)	Polyolefin copolymer electron beam crosslinked Comp 752
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

Specifications	EN 45545-2 Fire protection on railway vehicles
	EN 50264-1 Fire protection on railway vehicles
	EN 50306-1 Fire protection on railway vehicles
	NFPA 130 Fire protection on railway vehicles
	UN/ECE-R 118 fire protection for rolling stock
	EN 50306-4 Resistance to ozone
	EN 60811-504 High low temperature resistance
	EN 60811-404 High oil resistance
	EN 60811-404 High fuel resistance
	EN 60811-404 Alkali resistance
	EN 60811-404 Acid resistance
	DIN 51900 Low fire load
	EN 50618 UV resistant

## Commercial data

Packaging size	1
Net weight	845 g
Net weight	75 g/m
Country of origin	Switzerland
European customs tariff number	85444993
GTIN	5713140062221
ETIM	EC003249



**Pushing Performance**  
Since 1945

## Commercial data

eCl@ss

27061801 Data and communication cable (copper)

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09456000694](#)