

## M12 D-cod 4-pol st/st m/m Rail 1.4m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 222 2011 014
Specification	M12 D-cod 4-pol st/st m/m Rail 1.4m
HARTING eCatalogue	<a href="https://b2b.harting.com/09482222011014">https://b2b.harting.com/09482222011014</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 D-coding
	Male Straight
	Overmoulded
Connector 2	M12 D-coding
	Male Straight
	Overmoulded
Type of cable	Copper cable (round)
Description of the cable	for railway applications

### Version

Cable length	1.4 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

### Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Limiting temperature	-40 ... +85 °C unmoved
	-25 ... +70 °C moved



**Pushing Performance**  
Since 1945

## Technical characteristics

Cable diameter	6.6 mm $\pm$ 0.2 mm
Minimum bending radius	6x Cable diameter (repeated bending) 5x Cable diameter (singular bending)
Impedance	100 $\Omega$ $\pm$ 5 %

## Material properties

Material (cable)	Elastomer
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	EN 45545-2
----------------	------------

## Commercial data

Packaging size	10
Net weight	136.8 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140247765
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09482222011014](#) [9482222011014](#)