

M12 D-cod 4-pol an/- m/- Rail 10m



Image is for illustration purposes only. Please refer to product description.

Part number	09 48 800 0011 100
Specification	M12 D-cod 4-pol an/- m/- Rail 10m
HARTING eCatalogue	https://b2b.harting.com/09488000011100

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 D-coding
	Male Angled
	Overmoulded
Type of cable	Copper cable (round)
Description of the cable	for railway applications

Version

Cable length	10 m
Number of cores	4
Core structure	4x AWG 22/7
Coding	D-coding

Technical characteristics

Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s
	100 Mbit/s
Limiting temperature	-40 ... +85 °C unmoved
	-25 ... +70 °C moved
Cable diameter	6.6 mm ± 0.2 mm
Minimum bending radius	6x Cable diameter (repeated bending)
	5x Cable diameter (singular bending)



Pushing Performance
Since 1945

Technical characteristics

Impedance	100 Ω \pm 5 %
-----------	------------------------

Material properties

Material (cable)	Elastomer
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel

Specifications and approvals

Specifications	EN 45545-2
----------------	------------

Commercial data

Packaging size	2
Net weight	689 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140240001
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09488000011100](#) [9488000011100](#)