

## M12 L-cod 4+FE st/- f/- PUR 1,0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 310 0543 010
Specification	M12 L-cod 4+FE st/- f/- PUR 1,0m
HARTING eCatalogue	<a href="https://b2b.harting.com/21343100543010">https://b2b.harting.com/21343100543010</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 L-coding Female Straight
Type of cable	Copper cable (round)

### Version

Cable length	1 m
Number of cores	5
Core structure	5x 1.5 mm <sup>2</sup>
Coding	L-coding

### Technical characteristics

Rated current	12 A
Rated voltage	63 V DC
Limiting temperature	-25 ... +80 °C
Cable diameter	8.2 mm

### Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	760691ac-b4d2-427c-9996-5886190b813b
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

CE	Yes
----	-----

## Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85444290
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21343100543010](#)