




Mating face according to MIL-C-24308 / DIN 41 652 / CECC 75301-802


No. 1 contact




Printed board layout (1,6±0,2 thick)
View component side
(PCB plating = Tin)



No. 1 contact



Mounting force on Printed board : 25 - 80 N

A							Dat.		Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub male standard 25 poles with solder pins, screw-lock, board lock and grounding pins	Maßstab/ Scale 1,5:1
							Detail.	26-OCT-01	JB			
							Insp.					
							Stand.					
	09 66 362 6813	4-40 UNC	2									
	09 66 362 7813	4-40 UNC	3									
	09 66 362 5813	4-40 UNC	0,76 µm Au	29725	26-OCT-01	JB						
	Part number	screw-lock	Performance level	Mod.	Dat.	Name	HARTING EURL F-95972 Paris				TB 09 66 362 X81X Sub.	Blatt/ Page 3

09 66 362 7813
D-Sub - S PCB connector

Other applications

gender	male connector, right angled
Termination	Turned solder pins
shell	tinned metal shell with dimples
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with snap-in-clips
Grounding	with grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 362 5813
D-Sub - S PCB connector

Other applications

gender	male connector, right angled
Termination	Turned solder pins
shell	tinned metal shell with dimples
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with snap-in-clips
Grounding	with grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 362 6813
D-Sub - S PCB connector

Other applications

gender	male connector, right angled
Termination	Turned solder pins
shell	tinned metal shell with dimples
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with snap-in-clips
Grounding	with grounding board locks
flange	with screw lock UNC 4-40
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



Data sheets are available in following formats
2D files

Typenblatt

Typenblatt

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09663625813](#)