





5 4 3 2 1

Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802



PCB layout hole
component side
(PCB holes plating : Tin)



Connector retention and insertion forces on the PCB = 25 / 80 newtons

A

09 66 352 6615	M 3	2					Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub 25 poles low profil angle female,solder pin with nut and grounding board lock.	Maßstab/ Scale 1.5:1
09 66 352 7615	M 3	3				Detail.	02/sept/00	jfb			
09 66 352 5615	M 3	0.76 µm Au				Insp.					
09 66 352 6616	4-40 UNC	2	27961	24/nov/00	jfb	Stand.					
09 66 352 7616	4-40 UNC	3	27952	02/oct/00	jfb	HARTING EURL F-95972 Paris				TB 0966352x61x	Blatt/ Page 2 / 6
09 66 352 5616	4-40 UNC	0.76 µm Au	27948	02/sept/00	jfb						
Part number	Screw lock thread	Performance level	Mod.	Dat.	Name					Sub.	

HARTING EURL
F-95972 Paris

Sub.

09 66 352 5616
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 352 5615
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level S4
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.



Data sheets are available in following formats
2D files

Typenblatt

Typenblatt

09 66 352 6615
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 352 6616
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level 2
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 352 7615
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	M 3
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

09 66 352 7616
D-Sub - S PCB connector

Other applications

gender	female connector, right angled
Termination	Stamped solder pins - low profile
shell	tinned metal shell
Number of contacts	25 way
Row pitch	Row separation 2.54 mm
Board fixing	with grounding board locks
flange	UNC4-40
Performance level	Performance level 3
Material	PBTP

Note: Obligatory information about HARTING products can be obtained exclusively from the data sheets.

Inquiry

The data sheet is up to date

2D files

PDF

DXF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09663525616](#)