







X Kontaktbelegung
contact loading



09 02 132 5931	—	min.0,76µm (30µin) Au über/over min.1,27µm (50µin) Ni
09 02 132 4931	VG	Au über/over Ni
09 02 132 7931	3	Au über/over Ni
09 02 132 6931	2	Au über/over Ni
09 02 132 2931	1	Au über/over Ni
Bestell-Nr. Part-No.	Anforderungsstufe nach IEC performance level per IEC	Kontaktoberfläche Contact Plating

			All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maß/Free size tolerances siehe / see IEC 603-2		
				Dat.	Name	Maßstab/Scale 1 : 1 (2 : 1)	Bauform B Messerleiste Einlöt , 32 pol. <i>type B male connector solder , 32 pol.</i>				
			Detail.	11.07.00	Rie.						
			Insp.	11.07.00	Pa.						
			Stand.								
			HARTING KGaA D-32339 ESPELKAMP				TB 09 02 132 x931			Blatt/ page /	
28027											
Mod.	Dat.	Name									

09 02 132 6931
Printed board connector

Other applications

Type	Type B
Standard/Inverse	Standard
Contact gender	Male contacts
Size	Whole size
Number of contacts	32 poles
Contact arrangement	Row a
Termination	Angled solder pins
Termination length	3.0 mm
First mating contact	without first mating contacts
Performance Class	Performance level 2 as per IEC 60603-2
Contacts	with contacts
Row pitch	2.54 mm
Board fixing	Without fixing
Current	2 A max.
Clearance/Creepage	1.2 / 1.2 mm min.

Inquiry

Data sheets are available in following formats
2D files

PDF

DXF

09 02 132 2931
Printed board connector

Other applications

Type	Type B
Standard/Inverse	Standard
Contact gender	Male contacts
Size	Whole size
Number of contacts	32 poles
Contact arrangement	Row a
Termination	Angled solder pins
Termination length	3.0 mm
First mating contact	without first mating contacts
Performance Class	Performance level 1 as per IEC 60603-2
Contacts	with contacts
Row pitch	2.54 mm
Board fixing	Without fixing
Current	2 A max.
Clearance/Creepage	1.2 / 1.2 mm min.



Data sheets are available in following formats

2D files

Typenblatt

Typenblatt

09 02 132 7931
Printed board connector

Other applications

Type	Type B
Standard/Inverse	Standard
Contact gender	Male contacts
Size	Whole size
Number of contacts	32 poles
Contact arrangement	Row a
Termination	Angled solder pins
Termination length	3.0 mm
First mating contact	without first mating contacts
Performance Class	Performance level 3 as per IEC 60603-2
Contacts	with contacts
Row pitch	2.54 mm
Board fixing	Without fixing
Current	2 A max.
Clearance/Creepage	1.2 / 1.2 mm min.

Inquiry

Data sheets are available in following formats
2D files

PDF

DXF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[09021325931](#)