

Han Ex 3A Kit HBM angled/HTE-M20



Image is for illustration purposes only. Please refer to product description.

Part number	10 36 003 0004
Specification	Han Ex 3A Kit HBM angled/HTE-M20
HARTING eCatalogue	https://b2b.harting.com/10360030004

Identification

Category	Connector sets
Series	Han A [®]
Series of hoods/housings	Han [®] Ex
Element	Complete set

Version

Termination method	Screw termination
Size	3 A
Number of contacts	3
PE contact	Yes
Version	Top/side entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Connectors for explosion hazardous environments

Technical characteristics

Rated current	10 A
Rated voltage	90 V
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-20 ... +40 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP67 with seal screw 09 20 000 9918



Pushing Performance
Since 1945

Material properties

Material (insert)	Polycarbonate (PC)
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
Material (seal)	NBR
Material (locking)	Stainless steel
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
	IEC 60079-0
	EN 60079-11

Commercial data

Packaging size	1
Net weight	154.12 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140189690
ETIM	EC002636
eCl@ss	27440113 Rectangular connectors (set)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[10360030004](#)