

Material

- Item a Clamp: Steel zinc plated
- Item b Terminal screw: Brass Zinc plating “-” slot type
- Item c Female contact: PhBz Tin plated
- △ Item d With flange screw: Steel zinc plated M2.5 “+/-” slot type
- Item e Terminal (Up body): Thermoplastic (UL94V-0)
- Item f Terminal (Down body): Thermoplastic (UL94V-0)
- Item g Clampage: Steel Zinc plated
- Electrical cULus
- Voltage rating: 300VAC
- Current rating: 20A
- Wire range: 0.34-2.5mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In
- Screw: M2.5
- △ Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ Safety approval: 

POLES		G: Pb<40000ppm
02: 02 pole		
... ..	Color	0000: "@ " Logo (Standard)
16: 16 pole	0 Black (RAL9005)	(Steel screw plating Cr ³⁺)
	2 Red (RAL3001/D)	000A: "ANYTEK" Mark
	3 Orange(RAL2011/P)	Any special item by
	4 Yellow(RAL1018/A)	customer request.
	5 Green(RAL6018/T)	please contact sales
	6 Blue (RAL5015/A)	department.
	8 Grey(RAL7035/D)	

POLE		2	3	4	5	6	7	8
A		13.00	20.50	28.00	35.50	43.00	50.50	58.00
B		7.50	15.00	22.50	30.00	37.50	45.00	52.50
Tol.		±0.10			±0.20			
POLE	9	10	11	12	13	14	15	16
A	65.50	73.00	80.50	88.00	95.50	103.00	110.50	118.00
B	60.00	67.50	75.00	82.50	90.00	97.50	105.00	112.50
Tol.		±0.30			±0.40			

<h1>ANYTEK</h1>				<h2>CUSTOMER COPY</h2> <p>ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD</p>			
TITLE		VM 7.5 mm W/ Flange Series					
PART NO.		VMxxA5x3xxxG		DWG NO.		8VM0401	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
			Jacke 2010.03.23	Jacke 2009.10.10			X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
					UNIT: mm SCALE: NONE		
					SHEET: 01/01		REV.: E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VM02A5530000G</u>	<u>VM03A5530000G</u>	<u>VM04A5530000G</u>	<u>VM05A5530000G</u>	<u>VM06A5530000G</u>	<u>VM07A5530000G</u>
<u>VM08A5530000G</u>	<u>VM09A5530000G</u>	<u>VM10A5530000G</u>	<u>VM11A5530000G</u>	<u>VM12A5530000G</u>	<u>VM13A5530000G</u>
<u>VM14A5530000G</u>	<u>VM15A5530000G</u>	<u>VM16A5530000G</u>	<u>VM12A5830000G</u>	<u>VM15A5030000G</u>	<u>VM10A5830000G</u>
<u>VM10A5030000G</u>	<u>VM14A5830000G</u>	<u>VM15A5830000G</u>	<u>VM06A5030000G</u>	<u>VM14A5030000G</u>	<u>VM05A5830000G</u>
<u>VM03A5030000G</u>	<u>VM05A5030000G</u>	<u>VM04A5830000G</u>	<u>VM02A5030000G</u>	<u>VM08A5830000G</u>	<u>VM06A5830000G</u>
<u>VM02A5830000G</u>	<u>VM04A5030000G</u>	<u>VM08A5030000G</u>	<u>VM09A5830000G</u>	<u>VM13A5030000G</u>	<u>VM12A5030000G</u>
<u>VM13A5830000G</u>	<u>VM16A5030000G</u>	<u>VM03A5830000G</u>	<u>VM11A5030000G</u>	<u>VM16A5830000G</u>	<u>VM11A5830000G</u>
<u>VM07A5030000G</u>	<u>VM07A5830000G</u>	<u>VM09A5030000G</u>			