

SIGN	DATE	DESCRIPTION	APPROVER
△	2010.03.31	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item (a) Clamp: Brass(CuZn) Ni plated
- Item (b) Terminal screw: Steel Zinc plating “-” slot type
- Item (c) Female contact: PhBz ,Tin plated
- Item (d) Terminal (up body): Thermoplastic (UL94V-0)
- Item (e) Terminal (down body): Thermoplastic (UL94V-0)
- Item (f) With flange screw: M2.5 Steel Zinc plated.

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 4 Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 

EM xx A 1 x 2 xxxx G

No. OF POLES
02: 2 POLES
:
16: 16 POLES





Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G: Pb<40000ppm

0000: “@” Logo (Standard)
000A: “ANYTEK” Mark

Any special item by
customer request.
please contact sales
department.




POLE		2	3	4	5	6	7	8
A		13.00	20.50	28.00	35.50	43.00	50.50	58.00
B		7.50	15.00	22.50	30.00	37.50	45.00	52.50
Tol.	±0.10				±0.15			
POLE	9	10	11	12	13	14	15	16
A	65.50	73.00	80.50	88.00	95.50	103.00	110.50	118.00
B	60.00	67.50	75.00	82.50	90.00	97.50	105.00	112.50
Tol.	±0.20				±0.30			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EM-7.5 Series With flange								
PART NO.		EMxxA1x2xxxxG			DWG NO.	8EM0301				
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
			Jacke 2010.03.31	Jacke 2010.03.31			UNIT: mm		X. ±0.50	
							SCALE: NONE		X.X ±0.30	
					SHEET: 01/01		REV: C		X.XX ±0.10	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[EM02A1520000G](#) [EM03A1520000G](#) [EM04A1520000G](#) [EM05A1520000G](#) [EM06A1520000G](#) [EM07A1520000G](#)
[EM08A1520000G](#) [EM09A1520000G](#) [EM10A1520000G](#) [EM11A1520000G](#) [EM12A1520000G](#) [EM13A1520000G](#)
[EM14A1520000G](#) [EM15A1520000G](#) [EM16A1520000G](#)