


1	2	3	4	5	6	7	8																																																																																																																																														
A	har-flexicon female connector, vertical, screwing RoHS compliant			Cable connection <table><tr><td>Type</td><td>har-flexicon 3.50/3.81 FSV</td><td>har-flexicon 5.08 FSV</td></tr><tr><td>Part numbers</td><td>1431xx14401xxx & 1431xx15401xxx</td><td>1431xx17401xxx</td></tr><tr><td>Conductor size AWG max</td><td>14 AWG</td><td>12 AWG</td></tr><tr><td>Conductor size AWG min</td><td>30 AWG</td><td>30 AWG</td></tr><tr><td>Conductor size solid max</td><td>1.5 mm²</td><td>2.5 mm²</td></tr><tr><td>Conductor size solid min</td><td>0.05 mm²</td><td>0.05 mm²</td></tr><tr><td>Conductor size stranded max</td><td>1.5 mm²</td><td>1.5 mm²</td></tr><tr><td>Conductor size stranded min</td><td>0.05 mm²</td><td>0.05 mm²</td></tr><tr><td>Conductor size stranded for end sleeve</td><td></td><td></td></tr><tr><td>Stripping length max</td><td>6 mm</td><td>7.5 mm</td></tr><tr><td>Stripping length min</td><td>5 mm</td><td>6 mm</td></tr><tr><td>Screw thread</td><td>M2</td><td>M2</td></tr><tr><td>Tightening Torque max</td><td>0.25 Nm</td><td>0.6 Nm</td></tr><tr><td>Tightening Torque min</td><td>0.2 Nm</td><td>0.5 Nm</td></tr></table>				Type	har-flexicon 3.50/3.81 FSV	har-flexicon 5.08 FSV	Part numbers	1431xx14401xxx & 1431xx15401xxx	1431xx17401xxx	Conductor size AWG max	14 AWG	12 AWG	Conductor size AWG min	30 AWG	30 AWG	Conductor size solid max	1.5 mm ²	2.5 mm ²	Conductor size solid min	0.05 mm ²	0.05 mm ²	Conductor size stranded max	1.5 mm ²	1.5 mm ²	Conductor size stranded min	0.05 mm ²	0.05 mm ²	Conductor size stranded for end sleeve			Stripping length max	6 mm	7.5 mm	Stripping length min	5 mm	6 mm	Screw thread	M2	M2	Tightening Torque max	0.25 Nm	0.6 Nm	Tightening Torque min	0.2 Nm	0.5 Nm	A																																																																																																			
Type	har-flexicon 3.50/3.81 FSV	har-flexicon 5.08 FSV																																																																																																																																																			
Part numbers	1431xx14401xxx & 1431xx15401xxx	1431xx17401xxx																																																																																																																																																			
Conductor size AWG max	14 AWG	12 AWG																																																																																																																																																			
Conductor size AWG min	30 AWG	30 AWG																																																																																																																																																			
Conductor size solid max	1.5 mm ²	2.5 mm ²																																																																																																																																																			
Conductor size solid min	0.05 mm ²	0.05 mm ²																																																																																																																																																			
Conductor size stranded max	1.5 mm ²	1.5 mm ²																																																																																																																																																			
Conductor size stranded min	0.05 mm ²	0.05 mm ²																																																																																																																																																			
Conductor size stranded for end sleeve																																																																																																																																																					
Stripping length max	6 mm	7.5 mm																																																																																																																																																			
Stripping length min	5 mm	6 mm																																																																																																																																																			
Screw thread	M2	M2																																																																																																																																																			
Tightening Torque max	0.25 Nm	0.6 Nm																																																																																																																																																			
Tightening Torque min	0.2 Nm	0.5 Nm																																																																																																																																																			
B	General information <table><tr><td colspan="3">female connector</td></tr><tr><td>Type</td><td>har-flexicon 3.50/3.81 FSV</td><td>har-flexicon 5.08 FSV</td></tr><tr><td>Part numbers</td><td>1431xx14401xxx & 1431xx15401xxx</td><td>1431xx17401xxx</td></tr><tr><td>Contact pitch</td><td>3.5 mm & 3.81 mm</td><td>5.08 mm</td></tr><tr><td>No. of contacts</td><td>2-25 poles</td><td>2-25 poles</td></tr><tr><td>Rated surge voltage (II/2)</td><td>2,5 kV</td><td>4 kV</td><td>(overvoltage cat. II / pollution degree 2)</td></tr><tr><td>Rated surge voltage (III/2)</td><td>2,5 kV</td><td>4 kV</td><td>(overvoltage cat. III / pollution degree 2)</td></tr><tr><td>Rated surge voltage (III/3)</td><td>2,5 kV</td><td>4 kV</td><td>(overvoltage cat. III / pollution degree 3)</td></tr><tr><td>Rated Voltage</td><td>300 V</td><td>300 V</td><td></td></tr><tr><td>Rated voltage (II/2)</td><td>300 V</td><td>600 V</td><td>(overvoltage cat. II / pollution degree 2)</td></tr><tr><td>Rated voltage (III/2)</td><td>150 V</td><td>300 V</td><td>(overvoltage cat. III / pollution degree 2)</td></tr><tr><td>Rated voltage (III/3):</td><td>150 V</td><td>250 V</td><td>(overvoltage cat. III / pollution degree 3)</td></tr><tr><td>Working current</td><td>10 A</td><td>15 A</td><td></td></tr><tr><td>Usegroup B, rated voltage / current</td><td>300 V / 10 A</td><td>300 V / 15 A</td><td></td></tr><tr><td>Usegroup C, rated voltage / current</td><td>- / -</td><td>- / -</td><td></td></tr><tr><td>Usegroup D, rated voltage / current</td><td>300 V / 10 A</td><td>300 V / 15 A</td><td></td></tr><tr><td>Contact resistance</td><td colspan="3">max. 15 mOhm</td></tr><tr><td>Insulation resistance</td><td colspan="3">min. 10⁹ Ohm (500 V DC)</td></tr><tr><td>Temperature range</td><td colspan="3">-40°C ... +110°C</td></tr><tr><td>Termination technology</td><td colspan="3">screw</td></tr><tr><td>Insertion force</td><td colspan="3">max. 3 N</td></tr><tr><td>Withdrawal force</td><td colspan="3">min. 1,5 N</td></tr><tr><td>Hot plugging</td><td colspan="3">No</td></tr><tr><td>Vibration</td><td colspan="3">10-150Hz,0,35mm,5g 2h each axes -> No contact disturbance > 1µs</td></tr><tr><td>RoHS - compliant</td><td colspan="3">Yes</td></tr><tr><td>UL file</td><td colspan="3">E314677</td></tr></table>			female connector			Type	har-flexicon 3.50/3.81 FSV	har-flexicon 5.08 FSV	Part numbers	1431xx14401xxx & 1431xx15401xxx	1431xx17401xxx	Contact pitch	3.5 mm & 3.81 mm	5.08 mm	No. of contacts	2-25 poles	2-25 poles	Rated surge voltage (II/2)	2,5 kV	4 kV	(overvoltage cat. II / pollution degree 2)	Rated surge voltage (III/2)	2,5 kV	4 kV	(overvoltage cat. III / pollution degree 2)	Rated surge voltage (III/3)	2,5 kV	4 kV	(overvoltage cat. III / pollution degree 3)	Rated Voltage	300 V	300 V		Rated voltage (II/2)	300 V	600 V	(overvoltage cat. II / pollution degree 2)	Rated voltage (III/2)	150 V	300 V	(overvoltage cat. III / pollution degree 2)	Rated voltage (III/3):	150 V	250 V	(overvoltage cat. III / pollution degree 3)	Working current	10 A	15 A		Usegroup B, rated voltage / current	300 V / 10 A	300 V / 15 A		Usegroup C, rated voltage / current	- / -	- / -		Usegroup D, rated voltage / current	300 V / 10 A	300 V / 15 A		Contact resistance	max. 15 mOhm			Insulation resistance	min. 10 ⁹ Ohm (500 V DC)			Temperature range	-40°C ... +110°C			Termination technology	screw			Insertion force	max. 3 N			Withdrawal force	min. 1,5 N			Hot plugging	No			Vibration	10-150Hz,0,35mm,5g 2h each axes -> No contact disturbance > 1µs			RoHS - compliant	Yes			UL file	E314677			Packging unit <table><tr><th>Type of packaging</th><th>No. of poles (xx)</th><th>Quantity</th><th>MOQ</th><th>Index (xxx)</th><th>Remark</th></tr><tr><td>box</td><td>2</td><td>300</td><td>1</td><td>000 = green, 163 = black</td><td></td></tr><tr><td>box</td><td>3</td><td>200</td><td>1</td><td>000 = green, 163 = black</td><td></td></tr><tr><td>box</td><td>4 - 5</td><td>150</td><td>1</td><td>000 = green, 163 = black</td><td></td></tr><tr><td>box</td><td>6 - 12</td><td>100</td><td>1</td><td>000 = green, 163 = black</td><td></td></tr><tr><td>box</td><td>13 - 20</td><td>50</td><td>1</td><td>000 = green, 163 = black</td><td></td></tr><tr><td>box</td><td>21 - 25</td><td>25</td><td>1</td><td>000 = green, 163 = black</td><td></td></tr></table>				Type of packaging	No. of poles (xx)	Quantity	MOQ	Index (xxx)	Remark	box	2	300	1	000 = green, 163 = black		box	3	200	1	000 = green, 163 = black		box	4 - 5	150	1	000 = green, 163 = black		box	6 - 12	100	1	000 = green, 163 = black		box	13 - 20	50	1	000 = green, 163 = black		box	21 - 25	25	1	000 = green, 163 = black		B
female connector																																																																																																																																																					
Type	har-flexicon 3.50/3.81 FSV	har-flexicon 5.08 FSV																																																																																																																																																			
Part numbers	1431xx14401xxx & 1431xx15401xxx	1431xx17401xxx																																																																																																																																																			
Contact pitch	3.5 mm & 3.81 mm	5.08 mm																																																																																																																																																			
No. of contacts	2-25 poles	2-25 poles																																																																																																																																																			
Rated surge voltage (II/2)	2,5 kV	4 kV	(overvoltage cat. II / pollution degree 2)																																																																																																																																																		
Rated surge voltage (III/2)	2,5 kV	4 kV	(overvoltage cat. III / pollution degree 2)																																																																																																																																																		
Rated surge voltage (III/3)	2,5 kV	4 kV	(overvoltage cat. III / pollution degree 3)																																																																																																																																																		
Rated Voltage	300 V	300 V																																																																																																																																																			
Rated voltage (II/2)	300 V	600 V	(overvoltage cat. II / pollution degree 2)																																																																																																																																																		
Rated voltage (III/2)	150 V	300 V	(overvoltage cat. III / pollution degree 2)																																																																																																																																																		
Rated voltage (III/3):	150 V	250 V	(overvoltage cat. III / pollution degree 3)																																																																																																																																																		
Working current	10 A	15 A																																																																																																																																																			
Usegroup B, rated voltage / current	300 V / 10 A	300 V / 15 A																																																																																																																																																			
Usegroup C, rated voltage / current	- / -	- / -																																																																																																																																																			
Usegroup D, rated voltage / current	300 V / 10 A	300 V / 15 A																																																																																																																																																			
Contact resistance	max. 15 mOhm																																																																																																																																																				
Insulation resistance	min. 10 ⁹ Ohm (500 V DC)																																																																																																																																																				
Temperature range	-40°C ... +110°C																																																																																																																																																				
Termination technology	screw																																																																																																																																																				
Insertion force	max. 3 N																																																																																																																																																				
Withdrawal force	min. 1,5 N																																																																																																																																																				
Hot plugging	No																																																																																																																																																				
Vibration	10-150Hz,0,35mm,5g 2h each axes -> No contact disturbance > 1µs																																																																																																																																																				
RoHS - compliant	Yes																																																																																																																																																				
UL file	E314677																																																																																																																																																				
Type of packaging	No. of poles (xx)	Quantity	MOQ	Index (xxx)	Remark																																																																																																																																																
box	2	300	1	000 = green, 163 = black																																																																																																																																																	
box	3	200	1	000 = green, 163 = black																																																																																																																																																	
box	4 - 5	150	1	000 = green, 163 = black																																																																																																																																																	
box	6 - 12	100	1	000 = green, 163 = black																																																																																																																																																	
box	13 - 20	50	1	000 = green, 163 = black																																																																																																																																																	
box	21 - 25	25	1	000 = green, 163 = black																																																																																																																																																	
C	Isulator material <table><tr><td>Material</td><td>PA/PPA</td></tr><tr><td>Color</td><td>green</td></tr><tr><td>UL classification</td><td>UL 94-V0</td></tr><tr><td>Material group acc. to IEC 60664-1</td><td>I (CTI > 600)</td></tr></table>			Material	PA/PPA	Color	green	UL classification	UL 94-V0	Material group acc. to IEC 60664-1	I (CTI > 600)	1431xx14401xxx				C																																																																																																																																					
Material	PA/PPA																																																																																																																																																				
Color	green																																																																																																																																																				
UL classification	UL 94-V0																																																																																																																																																				
Material group acc. to IEC 60664-1	I (CTI > 600)																																																																																																																																																				
D	Contact material <table><tr><td>Contact material</td><td>Copper alloy</td></tr><tr><td>Plating termination zone</td><td>Ni</td></tr><tr><td>Plating contact zone</td><td>Sn</td></tr></table>			Contact material	Copper alloy	Plating termination zone	Ni	Plating contact zone	Sn					D																																																																																																																																							
Contact material	Copper alloy																																																																																																																																																				
Plating termination zone	Ni																																																																																																																																																				
Plating contact zone	Sn																																																																																																																																																				
E	Derating The current carrying capacity is limited by maximum temperature of materialsfor inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given,without exceeding the maximum temperature. Control and test procedures according to DIN IEC 60512-5							E																																																																																																																																													
F	HARTING Electronics GmbH D-32339 Espelkamp			All rights reserved Department EC PD - DE Created by TADJE Inspected by ZWAHR Standardisation HOFFMANN Date 2016-09-07 State Final Release Title har-flexicon female connector, vertical, screwing Doc-Key / ECM-Nr. 100579803/UGD/000/D 500000108598 Type DS Number 14312401201 Rev. D Page 1/1				F																																																																																																																																													
1	2	3	4	5	6	7	8																																																																																																																																														

		All Dimensions in mm Original Size DIN A3		Scale 1:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by TADJE		Inspected by ZWAHR		Standardisation HOFFMANN		Date 2016-09-07		State Final Release			
Department EC PD - DE		Title har-flexicon female connector, vertical, screwing								Doc-Key / ECM-Nr. 100579803/UGD/000/D 500000108598					
HARTING Electronics GmbH D-32339 Espelkamp				Type DS		Number 14312401201						Rev. D		Page 1/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

<u>14311214401000</u>	<u>14310414401000</u>	<u>14310214401000</u>	<u>14310614401000</u>	<u>14310814401000</u>	<u>14310314401000</u>
<u>14311014401000</u>	<u>14311114401000</u>	<u>14310514401000</u>	<u>14310914401000</u>	<u>14310714401000</u>	<u>14311314401000</u>
<u>14311914401000</u>	<u>14310717401000</u>	<u>14310917401000</u>	<u>14311117401000</u>	<u>14311217401000</u>	<u>14310817401000</u>
<u>14310617401000</u>	<u>14311017401000</u>	<u>14310217401000</u>	<u>14310415401000</u>	<u>14310215401000</u>	<u>14311215401000</u>
<u>14310315401000</u>	<u>14310515401000</u>	<u>14310815401000</u>	<u>14311115401000</u>	<u>14311015401000</u>	<u>14310615401000</u>
<u>14310715401000</u>	<u>14310915401000</u>	<u>14310317401000</u>	<u>14310517401000</u>	<u>14310417401000</u>	