




SIZE	Part Num.	Threading	Headscrew	Packaging
25	8655MH2501BLF	UNC 4.40	Black	BULK (see note 1)
	8655MH2501BKLF	UNC 4.40	Black	KIT (see note 2)
	8655MH2502BLF	M3	Grey	BULK
	8655MH2502BKLF	M3	Grey	KIT



1 KIT
SEE NOTE 2



NOTES:

Material and finish: Zinc die-cast
Nickel plated

Cable strain relief: Polycarbonate (UL94V-0)

Jackscrews:

- Headscrew : plastic, color according threading
- Body : metal, threading according tables

Temperature range: -40°C to 120°C
Cable diameter: 4,0 to 13,0mm
Attenuation factor: >40 dB between 30MHz and 1 GHz
Marking FCI logo: Height 6 mm for all versions

Covers screwing force (max): 100 Ncm
Jackscrew screwing force (max): 50 Ncm

Packaging notes (see tables):

- 1 - Bulk : Every spare part packaged per 100 or 200 into plastic bag.5 plastic bags per carton box.
1 plastic bag per part.
- 2 - Kit : 1 set of spare parts necessary to realise 1 kit into a plastic bag.
100 plastic bags per carton box.



NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.



DESIGNATION	REP.	09	15	25	37
COVER BOTTOM	1		1		
JACKSCREW	2		2		
STRAIN RELIEF	3		2		
COVER TOP	4		1		
SCREW POZIDRIVE	5		2		

spec ref		dr		Alexandre Parr	2009/05/20	projection	mm	size	A3	scale	3:2		
tolerance std ISO 406 ISO 1101	GENERAL TOLERANCES: ISO 2768-m		eng	Detouillon, Da	2021/06/30			ecn no	ELX-F-38514-1				
			chr	-	-			rel level			Released		
			appr	Wollin, Severi	2021/06/30			product family					
surface	linear	0.X	± /	Amphenol FCi	title	D-SUB METAL HOODS STRAIGHT			dwg no	10085962		rev	G
		0.XX	± /										
		0.XXX	± /										
	ISO 1302	angular	0°	± / °	www.fci.com	cat. no.	Product - Customer Drw			sheet 1 of 3			



SIZE	Part Num.	Threading	Headscrew	Packaging
09	8655MH0901BLF	UNC 4.40	Black	BULK (see note 1)
	8655MH0901BKLF	UNC 4.40	Black	KIT (see note 2)
	8655MH0902BLF	M3	Grey	BULK
	8655MH0902BKLF	M3	Grey	KIT



SIZE	Part Num.	Threading	Headscrew	Packaging
15	8655MH1501BLF	UNC 4.40	Black	BULK (see note 1)
	8655MH1501BKLF	UNC 4.40	Black	KIT (see note 2)
	8655MH1502BLF	M3	Grey	BULK
	8655MH1502BKLF	M3	Grey	KIT




SIZE	Part Num.	Threading	Headscrew	Packaging
37	8655MH3701BLF	UNC 4.40	Black	BULK (see note 1)
	8655MH3701BKLF	UNC 4.40	Black	KIT (see note 2)
	8655MH3702BLF	M3	Grey	BULK
	8655MH3702BKLF	M3	Grey	KIT




spec ref				dr		Alexandre Parr	2009/05/20		projection 		mm 		size		A3	scale		1:1											
tolerance std		GENERAL TOLERANCES: ISO 2768-m				eng		Detouillon, Da					2021/06/30		ecn no				ELX-F-38514-1										
ISO 406						chr		-		-		product family				rel level				Released									
ISO 1101						appr		Wollin, Severi		2021/06/30																			
surface 		linear		0.X		±/		Amphenol FCI		title		D-SUB METAL HOODS						dwg no		10085962		rev		G					
																										0.XX		±/	
																										0.XXX		±/	
ISO 1302		angular		0°		±/°		www.fci.com		cat. no.				Product - Customer Drw				sheet 2 of 3											

CABLING INSTRUCTIONS FOR CABLE Ø 4, 5, 7 or 9 mm


1- Use two halves of strain relief, different sizes can be mixed (Ø4,5,7 or 9)



2- Strip cable 18mm and shape to two pigtails




3- Attach the strain relief around the cable




CABLING INSTRUCTIONS FOR CABLE Ø > 9 to 11 mm

1- Use one half of strain relief, (Ø9).


4- Bend cable shielding back on outside of strain relief



5- Mount connector and cable into the backshell



6- Assemble the other half screwing force: 100 Ncm



spec ref				dr		Alexandre Parr	2009/05/20		projection		mm		size		A3	scale		3:2											
tolerance std		GENERAL TOLERANCES: ISO 2768-m				eng		Detouillon, Da	2021/06/30						ecn no				ELX-F-38514-1										
ISO 406						chr		-		-																			
ISO 1101						appr		Wollin, Severi		2021/06/30					product family				rel level				Released						
surface		linear		0.X		±/		Amphenol FCi		title		D-SUB METAL HOODS				dwg no		10085962				rev		G					
																										0.XX		±/	
ISO 1302		angular		0°		±/°		www.fci.com		cat. no.				Product - Customer Drw				sheet 3 of 3											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[8655MH2502BLF](#) [8655MH3702BLF](#)