



Pushing Performance
Since 1945

Han-Modular Twin hood side entry M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 14 002 0501
Specification	Han-Modular Twin hood side entry M25
HARTING eCatalogue	https://b2b.harting.com/19140020501

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® Twin
Type of hood/housing	Hood

Version

Size	Modular Twin
Version	Side entry
Cable entry	1x M25
Locking type	Single locking lever
Details	Rated voltage ≤630 V
	Rated impulse voltage ≤6 kV
	Pollution degree 3
	For a complete connector the specified voltage rating is the maximum level which can be achieved. In cases where the used module(s) do offer lower voltage ratings, then these lower ratings are valid. Higher voltage ratings in individual applications can be approved in coordination with HARTING.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated



Pushing Performance
Since 1945

Material properties

Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes

Specifications and approvals

Specifications	IEC 61984
Approvals	CE

Commercial data

Packaging size	1
Net weight	54 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140124318
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[19140020501](#)