

10087122-7XXLF






0.05μm Au FULL PLATED
OVER 1.27μm Ni MIN

INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 5

PIN STYLE	SIZE	MISSING PIN
06	2x3	
08	2x4	
09	2x4	POS 01
10	2x5	
14	2x7	
16	2x8	
18	2x9	
20	2x10	
26	2x13	
30	2x15	
34	2x17	
40	2x20	
44	2x22	
50	2x25	
60	2x30	
64	2x32	

NOTES:

- 1 - HOUSING MAT'L : GLASS FILLED THERMOPLASTIC. UL94V-0 COLOR: BLUE
- 2 - PIN MATERIAL : BRASS
- 3 - PRODUCT PACKAGED IN TUBES.
- 4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELLING:
 - MEETS PACKAGING SPECS AS PER GS-14-0004
 - d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
ltr ecn no dr date				tolerances unless otherwise specified						title			
A F08-0149 LMU 08.03.27				angles		linear .X ±0.3				QKIE SSLIM HDR			
B B-19070 LMU 14.10.15						.XX ±0.13				STR 0.05µm AU			
C B-19564 BVE 14.12.01						.XXX ±0.05		scale 2.5:1					
D F-28652 LMU 17.11.30				dr J.COMPAGNON 08.03.07		engr L.MULIN 08.03.07				dwg no		sheet 1 of 1	size
				chr						10087122		A3	
				appd L.MULIN 08.03.07						type		CUSTOMER Drawing	
sheet index		revision											
		sheet 17.11.30											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10087122-704LF](#) [10087122-706LF](#) [10087122-708LF](#) [10087122-710LF](#) [10087122-714LF](#) [10087122-716LF](#)
[10087122-726LF](#) [10087122-734LF](#) [10087122-740LF](#) [10087122-750LF](#) [10087122-760LF](#) [10087122-730LF](#)