






PART NUMBER
SEE NOTE 6



- NOTES:
- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMAL PLASTIC, UL94V-0, BLACK.
TERMINAL: COPPER ALLOY.
SHELL: COPPER ALLOY.
 - FINISH:
TERMINAL:
30u" GXT/Au ON CONTACT AREA.
100u" MATTE TIN ON SOLDER TAIL.
UNDER PLATING: 50u" Ni MIN. OVER ALL.
SHELL:
MATTE TIN OVER 50u" Ni OVER ALL.
100u" MATTE TIN MIN ON SOLDER TAIL OVER 50u" Ni.
 - THIS PRODUCT WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN;
 - FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
 - THE PRODUCT CAN BE USED FOR PIP PROCESS.
 - PART NUMBER DEFINITION:
10126196 - X 0X X LF
LEAD FREE
PACKING TYPE
B: TUBE
R: TAPE & REEL
01: DIM A=2.54
02: DIM A=2.00
PLATING CODE
1: 30u" GXT ON CONTACT AREA
2: 30u" Au ON CONTACT AREA

spec ref -				dr John Han		2013/07/17		<div>projection</div> <div></div> <div>MM</div> <div></div>		size A3		scale 1.000			
tolerance std ISO 406 ISO 1101 <div>TOLERANCES UNLESS OTHERWISE SPECIFIED</div>				eng Li-Qing Lei		2023/03/02				ecn no ELX-N-47655-1					
				chr -		-									
				appr Tim Yao		2023/03/06		product family -				rel level Released			
surface ISO 1302		linear		0.X		±0.3		Amphenol FCI		title USB 2.0 A TYPE RECEPTACLE OFFSET TYPE		dwg no 10126196		rev D	
				0.XX		±0.20									
				0.XXX		±0.10									
		angular		0°		±2°		www.fci.com		cat. no. -		Product - Customer Drw			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10126196-102RLF](#)