




PRODUCT NUMBER
73326-XXXLF

PLATING OPTION
1= GXT 0.76 μm
3= GOLD 0.76 μm
5= GOLD 1.27 μm

PACKAGE OPTION
1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG

TERMINAL LOADING
1= FULLY LOADED
2= POS 2,3,4,5
3= POS 1,2,5,6

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.



NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μm MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μm MINIMUM MATTE TIN OVER 1.27 μm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY


- THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.

c - LABELING:


- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004

- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.








CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family MOD JACK			
ltr				ecn no		dr		date		title			
H				F06-0240		DLE		06.07.18		SMT RA JACK 6 POS INSIDE			
J				F09-0070		LSA		09.07.23					
K				B-15798		JFA		13.09.09					
L				F-21888		AMA		15.09.09		±2'		scale 2:1	
D				LEGRAND		04.10.18		engr		P NIZZI		04.10.18	
F				F04-0363		DLE		04.10.18		chr		D LEGRAND 04.10.18	
G				F05-0247		DLE		05.09.12		appd		P NZ 04.10.18	
sheet index		revision		L	E	B							
		sheet		1	2	3							

PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1101		MOD-JACK
ltr	ecn no	dr	date	title
D	F80620	DLE	98.11.26	SMT RA JACK
E	F06-024Q	DLE	06.07.18	6 POS. INSIDE
			angles	linear
			mm	scale 1:1
			dr	D LEGRAND
			enr	P NIZZI
			chr	D LE
			app	P NZ
sheet	revision			
index	sheet			




dwg no	73326	sheet 2 of 3	size
			A3
type	CUSTOMER Drawing		



FCIconnect.com

Copyright FCI



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302		ISO 406 ISO 1101				MOD JACK	
ltr		ecr no		date		tolerances unless otherwise specified		title	
A		F04-0363		04.10.18		±0.13		SMT RA JACK	
B		F06-0240		06.07.18		mm		6 POS INSIDE	
				angles		linear		scale 2:1	
				±2°					
				dr		D LEGRAND		dwg no	
				engr		P NIZZI		sheet 3 of - size	
				chr		D LEGRAND		73326 A4	
				appd		P NZ		type	
								CUSTOMER Drawing	
sheet index		revision sheet							

form: A4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[73326-111LF](#) [73326-122LF](#) [73326-311LF](#) [73326-312LF](#) [73326-131LF](#)