



Pushing Performance
Since 1945

DIN 41626 female connector for 12 5Åm GI



Image is for illustration purposes only. Please refer to product description.

Part number	20 10 125 4222
Specification	DIN 41626 female connector for 12 5Åm GI
HARTING eCatalogue	https://b2b.harting.com/20101254222

Identification

Category	Contacts
Series	DIN 41626 har-modular®
Type of contact	FO contact
Description of the contact	for GI fibre 50/125 µm for ceramic ferrule 62.5/125 µm

Version

Gender	Female
Manufacturing process	Turned contacts

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes



Pushing Performance
Since 1945

Material properties

California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	1
Net weight	7 g
Country of origin	Germany
European customs tariff number	85367000
GTIN	5713140133563
eCl@ss	27440204 Contact for industrial connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[20101254222](#)