

1	2	3	4	5	6	7	8
<							

white/ orange

orange

white/ brown

brown

①

②

⑦

⑧

TIA/EIA 568 B

④

⑤

⑥

③

blue

white/ blue

orange

white/ green

①

②

⑦

⑧

INDUSTRIAL

X

X

⑥

③

x

x

blue

white

1	2	3	4	5	6	7	8	
A	 preLink® System 							A
B	Environment specification							
	Storage temperature range -40°C to +85°C (95% RH max.)							
	Operating temperature range -40°C to +85°C (95% RH max.)							
	Rapid change of temperature (IEC 60512-11-4) 5 cycles between -40°C and 85°C with 30 minutes dwell at temp. extremes and 1 minute transition between temperatures							
	Dry heat (IEC 60512-11-9) Temperature 85°C, duration 500 h							
	Damp heat cyclic (IEC 60512-11-12) 5 cycles at test temperature +55°C; Variant 2							
	Cyclic damp heat (IEC 60068-2-38) 25°C to 65°C; cold sub-cycle - 10°C		humidity 93 % RH		21 cycles, 1 cycle/24 h			
	Cold (IEC 60512-11-10) -40°C duration 2 h							
	Flow mixed gas test (IEC 60512-11-7) Duration 4 d, Method 4 (mated and unmated)							
	C	Vibration Sine (IEC 60512-6-4) 10 - 500 Hz; 0.35 mm; 50 m/s2		10 cycles / 2 h / 3 axis		No contact disturbances ≥ 1 µs		
Mechanical shock (IEC 60512-test 6c) Half sine shock 300 m/s2, duration 11 ms		3 shocks / both directions / 3 axis - totally 18 shocks		No contact disturbances ≥ 1 µs				
Mechanical shock (DIN EN 61373 Class 1 cat b) Half sine shock 5 g, duration 30 ms								
Additional test to fulfill DIN EN 50155 for railway equipment 5 shocks / both directions / 3 axis - totally 30 shocks								
Random vibration (DIN EN 61373 Class 1 cat b) 5 - 150 Hz / aeff = 5,72 m/s2 / ASD-Level: 0.964 (m/s2)2/Hz								
D	Additional test to fulfill DIN EN 50155 for railway equipment Duration 5 h							
	No contact disturbances ≥ 1 µs							
E								
F								
1	2	3	4	5	6	7	8	

Coating		A=	mm ²	V=	mm ³	m=	g	Mat.
	All Dimensions in mm		Scale	Free size tol.			Ref.	
	Original Size DIN A3		1:1				Sub.	
	All rights reserved		Created by	Inspected by	Standardisation	Date	State	
	Department EL PD		PREOTU	PRIESTER	ROEBEN	2021-09-07	Final Release	
HARTING			Title preLink System				Doc-Key / ECM-Nr.	
D-32339 Espelkamp			Type DS	Number 20820000000			Rev. H	Page 2/2

A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[20820009901](#) [20820000001](#) [20821010001](#) [20820000003](#) [20820009916](#) [20820009915](#) [20825000001](#)
[20825010001](#) [20820010002](#) [20820010001](#) [20820050001](#) [20820050002](#) [20820051214](#) [20821010010](#) [20820061218](#)
[20825000002](#) [20820000002](#) [20821020101](#) [20821010220](#) [20824000001](#) [20821040101](#) [20822040001](#)
[20820020001](#) [20820001210](#) [20821040045](#) [20820000005](#) [20820062001](#) [20820071100](#) [20820052001](#) [20821040001](#)
[20820000005XL](#) [20821010012](#)