

HAIIC MICA USB



Image is for illustration purposes only. Please refer to product description.

Part number	20 95 000 0002 00
Specification	HAIIC MICA USB
HARTING eCatalogue	https://b2b.harting.com/2095000000200

Identification

Series	HARTING IIC
Element	MICA
Specification	USB
Features	<div>Designed for the harsh industrial environment</div> <div>Tested according industry and railway standards</div> <div>Ready for software customisation</div> <div>Adaptable, upgradeable hardware</div> <div>Power over Ethernet (PoE)</div>

Version

Processor	1 GHz ARM
Memory	<div>1 GB RAM</div> <div>4 GB eMMC</div> <div>Up to 32 GB Flash (via Micro SD Card)</div>
Operating system	Linux
Fixing	<div>DIN rail mounting kit</div> <div>Wall mounting kit</div>
Diagnostic display	2 LEDs to visualise the device status

Termination data

Supply voltage	<div>12 V DC</div> <div>24 V DC</div>
Interfaces	Ethernet (TCP/IP) 10/100 Mbit/s

Technical characteristics

Limiting temperature	-25 ... +75 °C
----------------------	----------------



Pushing Performance
Since 1945

Technical characteristics

Storage temperature	-25 ... +85 °C
Relative humidity	5 ... 95 % Non-condensing

Material properties

Material (hood/housing)	Aluminium
Surface (hood/housing)	Powder-coated
Length	132 mm
Width	86 mm
Height	35 mm
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	EN 301489
CE	Yes

Commercial data

Packaging size	1
Net weight	680 g
Country of origin	Germany
European customs tariff number	84714100
eCl@ss	90909090 Interim classification (unspecified)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[2095000000200](#)