

## M8 PCB Adapter 4pol Pcod. female PaPC



Image is for illustration purposes only. Please refer to product description.

Part number	21 02 341 2418
Specification	M8 PCB Adapter 4pol Pcod. female PaPC
HARTING eCatalogue	<a href="https://b2b.harting.com/21023412418">https://b2b.harting.com/21023412418</a>

### Identification

Category	Connectors
Series	Circular connectors M8
Element	PCB connector

### Version

Termination method	Reflow soldering termination (THR)
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	P-coding
Details	Order housings separately
Pack contents	50 pieces in a tray

### Technical characteristics

Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$



Pushing Performance

## Technical characteristics

Ambient temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 61076-2-114
----------------	-----------------

## Commercial data

Packaging size	50
Net weight	7 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

21023412418