




REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
A		PROPOSAL	05/11/05	L.CHAN



FRONT VIEW



SIDE VIEW




RECOMMENDED P.C.B. LAYOUT

MATERIALS:  
HOUSING: HIGH TEMPERATURE RESISTANT NYLON  
FLAMMABILITY RATING UL 94V-0  
SOLDER REFLOW PROCESS COMPATIBLE

CONTACTS: PHOSPHOR BRONZE  
PLATING: 50 μ" [1.27 MICRONS]  
MIN. GOLD ON MATING SURFACES.  
50 μ" [1.27 MICRONS]  
MIN. NICKEL UNDERPLATE  
100 μ" [2.54 MICRONS]  
MIN. MATTE TIN ON CONTACT TAILS.

PART NUMBER: RJE01-660-02

CONTACTS:  
6 = 6 CONTACTS LOADED IN POSITION 1 TO 6.



RECOMMENDED PANEL CUTOUT

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION  
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING  
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

DRAWN PAULW	DATE 05/11/04	Amphenol Canada Corp.		
DESIGNED		TITLE HIGH SPEED MODULAR JACK, 2 PORTS, EMI QUIET, 6 POSITION, 6 CONTACTS, UNSHIELDED - RoHS COMPLIANT		
CHECKED CHIGOW	05/11/04			
I. E. APPRD.				
Q. A. APPRD.				
DWG. APPRD.				
ENG. REL. NO.				
REF.				
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554	SCALE		
		WT. -----	SURF. -----	SHEET 1 OF 1

Amphenol Canada Corp.

TITLE HIGH SPEED MODULAR JACK,  
2 PORTS, EMI QUIET, 6 POSITION, 6 CONTACTS,  
UNSHIELDED - RoHS COMPLIANT

DWG DRAWING NO. P-RJE01-660-02 REV. A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RJE01-660-02](#)