



Pushing Performance  
Since 1945

# PCB receptacle fem. L-cod(60pcs) w/o FE



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 396 2506
Specification	PCB receptacle fem. L-cod(60pcs) w/o FE
HARTING eCatalogue	<a href="https://b2b.harting.com/21033962506">https://b2b.harting.com/21033962506</a>

## Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	PCB adapter
Specification	Straight

## Version

Termination method	Reflow soldering termination (THR)
Gender	Female
Shielding	Shielded
Number of contacts	4
Coding	L-coding
Details	Order housings separately
Pack contents	60 pieces in a tray

## Technical characteristics

Rated current	16 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Overvoltage category	III
Insulation resistance	>10 <sup>8</sup> Ω
Contact resistance	≤10 mΩ



**Pushing Performance**  
Since 1945

## Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥100
Isolation group	I (600 ≤ CTI)

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-111
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

## Commercial data

Packaging size	60
Net weight	8 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140228450
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21033962506](#)