



1	2	3	4	5	6	7	8	
A	 M12 A-cod an/- f/- shld. 							A
Technische Daten:								
Bemessungsspannung: IEC 61076-2-101				60 V				
Strombelastbarkeit: IEC 61076-2-101				4 A / 40°C				
B	Isolationswiderstand: IEC 60512			>=100 MΩ				
Verschmutzungsgrad: IEC 60664-1				3/2				
Schutzart: IEC 60529				IP 67, im verschraubten Zustand				
Umgebungstemperatur: EN 60512-11-10 EN 60512-11-4				-25°C ... +80°C -40°C -40°C ... +85°C				
C	Steckzyklen: IEC 60512-9a			>=100				
Kabeleigenschaften:								
Umgebungstemperatur:								
fest verlegt				-25°C ... +80°C				
bewegt				-5°C ... +80°C				
Kabel:				TPU, UL 20549, schwarz, 5x0,34mm ² , LiF9YH-C11YH				
D	Werkstoffe:							
Kontakt:				CuZn, Ni b / Au 0,2 gal.				
Kontaktträger:				PA, UL 94 V-0				
Überwurfmutter:				GD-Zn, Ni				
Griffkörper:				TPU, UL 94 HB, schwarz				
E	Montagedaten:							
empfohlenes Drehmoment:				0,6 Nm				
F								F
1	2	3	4	5	6	7	8	





	All Dimensions in mm	Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved Department HCS - RO	Created by STOCHECIC Stochei	Inspected by COSTEA Costea	Standardisation MUNTEANV Muntean	Date 2019-03-05	State Final Release	
HARTING Customised Solutions D-32339 Espelkamp		Title M12 A-cod an/- f/- shld.				Doc-Key / ECM-Nr. 100803046/UGD/000/A 500000148324	
		Type DS	Number 21347700568XXX			Rev. A	Page 1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[21347700568030](#)