

PERFORMANCE

Range 0 - 100 ppm
Maximum overload..... 500 ppm H₂S
Sensitivity 600 - 1000 nA/ppm H₂S
Zero in air at 20 °C..... <±0.6 ppm H₂S
Resolution..... 0.1 ppm H₂S
Linearity linear across range
Response time, t₉₀ <35 s
Long-term output drift..... <2% signal/month
Warranty 2 years

OPERATING CONDITIONS

Temperature range -20 to +50 °C
Operating humidity 15 - 90% RH (non-condensing)
Pressure range 90 - 110 kPa (nominal)
Operating circuit..... see Electrochemical Toxic Sensor Application Note
Applied potential 0 V
Storage life..... 6 months in original packaging (0 - 25 °C)

PHYSICAL CHARACTERISTICS

Label colour silver
Weight..... 5 g approx.
Dimensions see outline

This device is designed to be RoHS compliant.

CROSS-SENSITIVITY DATA




GAS	Concentration (ppm)	Sensor Response (As ppm H ₂ S)
Carbon Monoxide	300	<1.5
Sulfur Dioxide	5	<1
Nitric Oxide	35	<0.7
Nitrogen Dioxide	5	<-1
Hydrogen	100	0

Important Note

Do not solder to the connector pins as this may damage the sensor and thereby invalidate the warranty.

Details on recommended connector pins can be found in the Frequently Asked Questions within the Gas Sensor section of the SGX website.


OUTLINE




All dimensions in mm.
All tolerances ±0.15mm unless otherwise stated.

TEMPERATURE DEPENDENCE

EC-4-100-H2S Graph of Zero vs Temperature



EC-4-100-H2S Graph of Net Sensitivity vs Temperature



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[EC4-100-H2S](#)