



Pushing Performance  
Since 1945

# Ha-VIS eCon 2080GX-I-AW



Image is for illustration purposes only. Please refer to product description.

Part number	24 14 408 0001
Specification	Ha-VIS eCon 2080GX-I-AW
HARTING eCatalogue	<a href="https://b2b.harting.com/24144080001">https://b2b.harting.com/24144080001</a>

## Identification

Series	Ha-VIS eCon 2000
Identification	Advanced
Element	Industrial Ethernet Switches
Specification	Unmanaged
Type of Ethernet	Full Gigabit Ethernet

## Version

Total number of ports	8
Fixing	Wall mounting flat
Switching technology	Store and Forward
Frame size	10 kB
MAC table size	8k Entries
MAC-address filter	LLDP and PROFINET PTCP Delay (01-80-C0-00-00-0E) blocked
Packet buffer size	4 Megabit
Non blocking	Yes
Quality of service	Yes
Flow control	Off
Signal contact	No
PoE functionality	No
Jumbo frame support	Yes
Field of application	Indoor usage



**Pushing Performance**  
Since 1945

## Version

Pack contents	Pluggable and screwable Push-In contact for power supply Assembly instructions
---------------	---

## Termination data

Nominal voltage	24 V DC 48 V DC
Permissible voltage	9 ... 60 V DC
Surge protection	Yes
Operating current	190 mA @ 24 V DC 100 mA @ 48 V DC
Supply circuit	SELV (Circuit Breaker 10 A)
Starting current	1.2 A @ 24 V DC 2.7 A @ 48 V DC
Overcurrent protection	4 A At input
Power consumption	4.6 W @ 24 V DC 4.8 W @ 48 V DC
Termination method	Pluggable and screwable Push-In contact for power supply
Number of contacts	3
Conductor cross-section	0.14 ... 1.5 mm <sup>2</sup>
Conductor cross-section	AWG 30 ... AWG 14
Pinout	+ / - / FE
Reverse polarity protection	Yes

## Technical characteristics

Operating temperature	-40 ... +70 °C
Storage temperature	-40 ... +85 °C
Relative humidity	0 ... 95 % Non-condensing (operation) 0 ... 95 % Non-condensing (storage/transport)
Air pressure	≥795 hPa ≈ 2000 m
Degree of protection acc. to IEC 60529	IP30 mated condition

## Ethernet ports copper

10/100/1000 Mbit/s (ix Industrial <sup>®</sup> -Ports)	8
Transmission standard	10BASE-T 100BASE-TX 1000BASE-T
Auto-negotiation	Yes



**Pushing Performance**  
Since 1945

## Ethernet ports copper

Auto-polarity	Yes
Auto-MDI(X)	Yes
Transmission physics	Twisted Pair Cat. 5
Data rate	10 Mbit/s
	100 Mbit/s
	1,000 Mbit/s
Transmission length	100 m

## Material properties

Material (hood/housing)	Aluminium (anodised)
Length	24 mm
Width	80.4 mm
Height	113 mm
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead



**Pushing Performance**  
Since 1945

## Specifications and approvals

Specifications	EN 61000-6-1 EMC Interference immunity
	EN 61000-6-2 EMC Interference immunity
	EN 55024 EMC Interference immunity
	EN 61000-4-2 Electrostatic discharge (ESD)
	EN 61000-4-3 Electromagnetic field
	EN 61000-4-4 Rapid transients (burst)
	EN 61000-4-6 conducted disturbances
	EN 61000-6-4 emission standard
	EN 55032 emission standard
	FCC 47 FCR Part 15
	IEC 60721-3-3 Mechanical stability (class 3M4)
	IEC 60068-2-6 Vibration (sinusoidal)
	IEC 60068-2-27 Shock
UL / CSA	IEEE 802.3
	IEC 61076-3-124 Type A
	UL in preparation
Approvals	CE
	DNV GL in preparation
	E1 in preparation
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	181 g
Country of origin	Germany
European customs tariff number	85176200
GTIN	5713140194984
ETIM	EC000734
eCl@ss	19170130 Network switch (general application)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[24144080001](#)