





RoHS Compliant

| Rev.                                           | SIGN | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|------|-------------|----------|
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |      |             |          |

Technical Specification:

- 1. Current: 150A.
- 2. Torque: 15 lbf.in.
- 3. Mark"▲" is the Critical dimension.



|      |           |                                |      |
|------|-----------|--------------------------------|------|
| ①    | Spacer    | Steel , Matte Tin Plated       | 1PCS |
| ②    | terminal  | Copper alloy, Matte Tin Plated | 1PCS |
| ITEM | PART NAME | DESCRIPTION                    | Q'ty |

**Amphenol**  
**ANYTEK**

**CUSTOMER COPY**  
ALL RIGHT'S RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO.,LTD

|          |            |                             |                                                                                     |             |                                                                                     |            |       |
|----------|------------|-----------------------------|-------------------------------------------------------------------------------------|-------------|-------------------------------------------------------------------------------------|------------|-------|
| TITLE    |            | AMT45003DB Stamped terminal |                                                                                     |             |                                                                                     |            |       |
| PART NO. |            | AMT0450003DB0000G           |                                                                                     | DWG NO.     |                                                                                     | 8AMT0001   |       |
| APPROVED | CHECKED    | DESIGNED                    | DRAWN                                                                               | CUST NO.    |  | Tolerance  |       |
|          |            |                             |                                                                                     |             |                                                                                     | >30        | ±0.60 |
|          |            |                             |                                                                                     |             |                                                                                     | 6-30       | ±0.40 |
|          |            |                             |                                                                                     |             |                                                                                     | 0-6        | ±0.30 |
|          |            |                             |                                                                                     |             |                                                                                     | ANGLES ±1° |       |
|          | Seamus     | Seamus                      |  | UNIT: mm    |                                                                                     |            |       |
|          | 2023.10.16 | 2023.10.16                  |  | SCALE: NONE |                                                                                     |            |       |
|          |            |                             |                                                                                     |             | SHEET: 01/01                                                                        | REV: A0    |       |

PCB LAYOUT

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AMT0450003DB0000G](#)