

## Hyb.Cab.2XFO MM 50µm+3x2,5qmm;reel 500M



Image is for illustration purposes only. Please refer to product description.

Part number	33 57 851 5000 002
Specification	Hyb.Cab.2XFO MM 50µm +3x2,5qmm;reel 500M
HARTING eCatalogue	<a href="https://b2b.harting.com/33578515000002">https://b2b.harting.com/33578515000002</a>

### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Hybrid cable (copper/FO)
Description of the cable	Multimode

### Version

Cable length	500 m
Core structure	2x G50 / 125 µm 3x 2.5 mm <sup>2</sup>

### Technical characteristics

Cable diameter	12.6 mm
Minimum bending radius	10x Cable diameter (repeated bending) 5x Cable diameter (singular bending)

### Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Commercial data

Packaging size	1
Net weight	110 kg
Net weight	217 g/m
Country of origin	Germany
European customs tariff number	85447000
ETIM	EC001579
eCl@ss	27060501 Hybrid cable

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[3357851500002](#)