




Number of contacts

Mounting height

9–37
50






Turned solder pins, angled with/without snap-in-clips and grounding board locks

D-Sub - S

Identification	No. of contacts	Part No.	
Performance levels Explanations see page 02.02 Other performance levels on request		Performance level 3	Performance level 2
Male connector metal shell with dimples		2.84 mm pitch	2.84 mm pitch
With snap-in clips and grounding board locks	9	09 66 163 781 .	09 66 163 681 .
	15	09 66 263 781 .	09 66 263 681 .
	25	09 66 363 781 .	09 66 363 681 .
	37	09 66 463 781 .	09 66 463 681 .
	50	09 66 563 781 .	09 66 563 681 .
 available on request		2.54 mm pitch	2.54 mm pitch
	9	09 66 162 781 .	09 66 162 681 .
	15	09 66 262 781 .	09 66 262 681 .
	25	09 66 362 781 .	09 66 362 681 .
	37	09 66 462 781 .	09 66 462 681 .
	50	09 66 562 781 .	09 66 562 681 .
Without snap-in clips and grounding board locks		2.84 mm pitch	2.84 mm pitch
	9	09 66 123 780 .	09 66 123 680 .
	15	09 66 223 780 .	09 66 223 680 .
	25	09 66 323 780 .	09 66 323 680 .
	37	09 66 423 780 .	09 66 423 680 .
	50	09 66 523 780 .	09 66 523 680 .
 available on request		2.54 mm pitch	2.54 mm pitch
	9	09 66 122 780 .	09 66 122 680 .
	15	09 66 222 780 .	09 66 222 680 .
	25	09 66 322 780 .	09 66 322 680 .
	37	09 66 422 780 .	09 66 422 680 .
	50	09 66 522 780 .	09 66 522 680 .
Please insert digit for flange thread or fitted female screw locks			
M3 ▶	1		
4-40 UNC ▶	2		
fitted screw locks 4-40 UNC ▶	3		

Mounting height

9-37
50



Turned solder pins, angled with/without snap-in-clips and grounding board locks

Identification

Drawing

Dimensions in mm

Male connector


With snap-in clips
and grounding board locks

Without snap-in clips
and grounding board locks


Board drillings

9-37 50

Mating face acc. to: DIN 41 652 · CECC 75 301-802 · IEC 60 807
No. 1 contact





Grounding pins 0.2 x 0.6




7
Dimples

9-37 50

Mating face acc. to: DIN 41 652 · CECC 75 301-802 · IEC 60 807
No. 1 contact



7
Dimples



	a	b _{±0.1}	c	f
9	30.90	25.00	12.90	2.74
15	39.20	33.30	12.90	2.74
25	53.10	47.00	12.90	2.76
37	69.40	63.50	12.90	2.76
50	67.00	61.10	15.70	2.76

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING:

09665237803