

[illegible]

alle Löcher
all holes

 $\varnothing 1 \pm 0,1$

Position
position

c	d	—
a	b	—
	z	—
Reihe		
row		

$$4 \times \boxed{2,54} \quad (=10,16)$$

2,54

 $\phi 2,8^{+0,1}$
$$31 \times \boxed{2,54} \quad (=78,74)$$
 $88,9 \pm 0,1$

2,54		
------	--	--

$\equiv$	0,1	A
----------	-----	---

 $87,4 \pm 0,1$
$$31 \times 2,54 (=78,74)$$

2,54

Reihe
rowPosition
position

32

 $85,25 \pm 0,05$

$\phi 2,55 \pm 0,05$

 $88,9 \pm 0,1$

A

 $93,9 \pm 0,1$

X ▲

A-A (2:1)

Montageloch Mittellinie
mounting hole center-line

Nacheiler
lagging pin 0,6 mm

Standard
standard pin

Voreiler
preleading pin

Standard
standard pin

Voreiler
preleading p

Steckbedingungen entsprechen nicht IEC 61076-4-113
mating conditions not acc. to IEC 61076-4-113

X
Kontaktbelegung
contact loading

— d
— c
— b
— a
— 7

32 30 28 26 24 22 20 18 16 14 12 10 8 6 4 2

01 02 03 04 05 06 07 08 09 10 11 12 13 14 15 16

1 weitere Informationen siehe: DS 02 01 120 02 01
further information see: DS 02 01 120 02 01

			All Dimensions in mm Original Size DIN A 3				Techn. Character.		
36504	26.04.12	Hage.		Dat.	Name	Maßstab/Scale 1 : 1			
35551	10.08.09	Hage.	Detail.	05.11.97	Hm.				
32687	26.04.05	Hage.	Insp.	05.11.97	Pa.				
32460	25.01.05	Leh.	Stand.						
31412	09.04.03	Hage.	HARTING Electronics GmbH & Co. KG D-32339 ESPELKAMP						
30920	10.04.02	Rie.							
Mod.	Dat.	Name							

02 01 160 <u>2</u> 103	2
02 01 160 <u>1</u> 103	1
Bestell-Nr. <i>part-no.</i>	Anforderungsstufe <i>performance level</i> 

Nicht tolerierte Maße/Free size tolerances	
IEC 61076-4-113	
<i>har-bus 64 male connector</i> <i>without polarisation</i> <i>solder 160-pole SMC</i>	
TB 02 01 160 x103 Sub.	Blatt/ page 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HARTING:](#)

[02011601103](#)