



NOTES:

1. MATERIALS OF CONSTRUCTION:
BODY - BRASS, NICKEL PLATING
CONTACT PIN - BRASS, SILVER PLATING
CONTACT PIN - PHOSPHOR BRONZE, SILVER PLATING
INSULATOR - PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC 0-4 GHZ
C. VSWR: 1.5, MAX.
D. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
AS	SEE SHEET 1	6/4/99	42267	CPM
AT	STAMP "AMPHENOL" WAS "74868"\RD-DM12092001R3	19-Oct-12	49078	SH



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°	MATERIAL		DRAWN R. MAO	DATE 21-Jun-12	TITLE BNC "T" ADAPTOR JACK-PLUG-JACK UG-274/U		Amphenol RF	
	REFERENCE AND CONFIGURATION LEVEL:		ENGINEER S. LI	DATE 21-Jun-12			www.amphenolrf.com	
			APPROVED S. HSIEH	DATE 21-Jun-12			DRAWING NO. 31-8-NTS	
			CAD FILE				ITEM NO. 019073AAA00NJ5F	
			FINISH	I:\BNC\31-8-NTS	SCALE: 4.0:1.0 DWG SIZE B REV AT		PART NO. 31-8	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[031-8](#)