

5

4

3


2

1


NOTES:

- 1. MATERIALS AND FINISHES:
RP TNC STR PLUG - BRASS, NICKEL PLATING
CABLE - LMR 400
- 2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
- 3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-850-229-XXX AND DATE CODE"

REVISIONS				
REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	24-JUN-20	15247	EH



SCALE 0.400



LENGTH TABLE		
PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH 'L' IN INCHES [METERS]
95-850-229-012	-	12.00 [0.305]
95-850-229-024	-	24.00 [0.610]
95-850-229-036	-	36.00 [0.914]
-	95-850-229M100	39.37 [1.000]
95-850-229-048	-	48.00 [1.219]
95-850-229-072	-	72.00 [1.829]
-	95-850-229M200	78.74 [2.000]
-	95-850-229M300	118.11 [3.000]
-	95-850-229M400	157.48 [4.000]

TOLERANCE TABLE	
LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.90" [0 - 0.607]	±0.25" [0.006]
24.00" - 59.00" [0.610 - 1.499]	±0.50" [0.013]
5.0' - 24.9' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS:

<input checked="" type="checkbox"/> FREQUENCY: DC - 8 GHz	<input checked="" type="checkbox"/> CONTINUITY
<input type="checkbox"/> VSWR: _____ 1 MAX.	<input checked="" type="checkbox"/> HI-POT: 750 VRMS
<input type="checkbox"/> INS. LOSS: _____ dB MAX.	<input type="checkbox"/> OTHER

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE: <0.5mm = ±0.05mm [± 0.020 = ±0.002] >0.5 - 6mm = ±0.1mm [± 0.020 - 0.236 = ±0.004] >6.00 - 30mm = ±0.2mm [± 0.236 - 1.181 = ±0.008] >30.00 - 120mm = ±0.3mm [± 1.181 - 4.725 = ±0.012]		MATERIAL SEE NOTES		TITLE RP TNC STR PLUG TO RP TNC STR PLUG USING LMR 400 CABLE VARIOUS LENGTH		Amphenol RF	
THIRD ANGLE PROJ. REFERENCE		ANGLES = ±1°		ENGINEER KRISHNA S		DATE 14-MAY-20		SHEET NO. 2 OF 2 SCALE: 1.4:1.0	
EAR# EAR # 9189						SIZE B		DRAWING NO. 95-850-229-XXX ITEM NO. 95-850-229-XXX PART NO. 95-850-229-XXX	

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[095-850-229-012](#) [095-850-229M300](#) [095-850-229-048](#) [095-850-229M100](#) [095-850-229-024](#) [095-850-229M400](#)
[095-850-229-072](#) [095-850-229-036](#) [095-850-229M200](#)