







Notes:

- Material and Finish:
 - Receptacle Housing & Protective Cover: Zinc Die-Cast, Nickel Plated
 - Ball Chain Assembly: Copper Alloy and Stainless Steel, Nickel Plated
 - Panel Nut: Brass, Finish: Nickel Plated
 - Panel Gasket: Silicon, Color: White
 - Duplex LC Adaptor Assembly:
 - Housing: Mod. PPO, UL94 V-0, Color: SM Blue/MM Beige/APC SM Green
 - Alignment Sleeves: SM Ceramic/MM Phosphor Bronze
 - Dust Cap: PP, Color: Neutral transparent
 - Operating Temperature: -40°C to +85°C
- Connector can be front or rear mounted to a maximum panel thickness of 3.2mm.
- IP67 rated when covered or fully mated with the appropriate mating connector

Directive 2002/95/EC RoHS Compliant

Description	Part Number
Nickel Plated Die-Cast Duplex LC Single Mode Receptacle + Cover Assembly	17-300380
Nickel Plated Die-Cast Duplex LC Multi Mode Receptacle Cover Assembly	17-300390
Nickel Plated Die-cast Duplex LC APC Single Mode Receptacle Cover Assembly	17-300400

Customer:			Tolerance Unless otherwise specified		Autodesk Inventor	Scale:	Dim. in mm
Name	Title	Approval Date	0	PLC	± 0.30		
			1	PLC	± 0.20	Material: See Notes	Title: IP67 Industrial Duplex LC Receptacle + Cover Assembly Kit Nickel Plated Die-Cast Version
			2	PLC	± 0.10		
			3	PLC	± 0.05		
			ANGLES		± 1°	Drawing No.: 17K1A302	DIN A3
			D-old				
a	original					Part No.: SEE PART NUMBER TABLE	Sheet 1/1
Rev.	Changes	Date	Name				

CONEC®

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[17-300400](#) [17-300380](#) [17-300390](#)