


NOTICE OF PROPRIETARY RIGHTS THIS DOCUMENT CONTAINS CONFIDENTIAL TECHNICAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

SYM	REVISION DESCRIPTION	DFTM	DATE	APPD	DATE
A	RELEASED FOR PRODUCTION	D. J. H.	10/17/13	J. D. B.	10/21/13
B	CHANGED PER CDC #43318	N. N. N	11/4/15	J. D. B.	12/11/15



1.0 PERFORMANCE
 1.1 FREQUENCY RANGE: DC-6 GHz
 1.2 NOMINAL IMPEDANCE: 50 OHMS
 1.3 DWV: 750 VRMS @ 60 Hz (SEA LEVEL)
 1.4 TEMPERATURE RANGE: -65°C TO +165°C

2.0 MATERIALS
 2.1 DIELECTRIC: PTFE/REXOLYTE
 2.2 CONTACT: BRASS
 2.3 LOCKING RING: PHOSPHOR BRONZE
 2.4 CRIMP FERRULE: SOFT COPPER
 2.5 OTHER METAL PARTS: BRASS
 2.6 GASKET: SILICONE RUBBER
 2.7 HEAT SHRINK: POLYOLEFIN THICK WALL

3.0 FINISHES: SEE TABLE

4.0 MECHANICAL
 4.1 INTERFACE PER
 MIL-STD-348

BODY	CONTACT
ALBALOY	GOLD/NI

MATL:		UNLESS OTHERWISE SPECIFIED		DFTM.	D. J. H.				TIMES MICROWAVE SYSTEMS				
		ALL DIMENSIONS ARE IN INCHES MACHINED SURFACES FINISH N/A RMS MAX. REMOVE ALL BURRS .005 MAX. BREAK MACHINE CORNERS .005 MAX. FILLET R. TOLERANCES ON DECIMALS .XX ± .03 .XXX ± .005 ANGLES ± 1° FRACTIONS ± 1/32		DATE	10/17/13		CHKD.	J. D. B.					
USED ON: C				DATE	10/21/13		TC-240-NMH-X N MALE FOR LMR-240 CABLE SOLDER/CRIMP/NO BRAID TRIM						
				APPD.	J. D. B.								
SCALE:	N/A	DWG. SIZE	A	DO NOT SCALE DRAWING	CODE IDENT	68999	DATE	10/21/13	SHEET	1 of 1	SD3190-2887	REV	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TC-240-NMH-X](#)