




I. MATERIALS & FINISHES

Components	Materials	Finishes	Thk. (μ")
Body	Brass	Albaloy	80
Center Cont.	QBe2	Gold	50
Ferrule	Brass	Albaloy	80
Nut	Brass	Albaloy	80
Insulator	PTFE	--	--
Gasket	Silicone	--	--

III. ENVIRONMENT PROPERTIES

Temperature Range:	-40°c~+125°c
Thermal Shock:	MIL-STD 202G, Meth.107, Cond.B
Vibration:	MIL-STD 202G, Meth.204, Cond.D
Shock:	MIL-STD 202G, Meth.213, Cond I
Climatic Class:	IEC 60068 55/155/21
(2002/95/EC)RoHS:	Compliant

V. TOOLING


Stripping Tool: 3192-102/CST-195/200
Crimping Tool: 3190-667/CT-240/200/100

II. ELECTRICAL PROPERTIES


Impedance (Ω):	50
Frequency Range (GHz):	DC to 6 GHz
Dielectirc Withstanding Voltage (V):	1000
Insulation Resistance (MΩ):	≥5000
VSWR:	≤1.30
Insertion Loss(dB, f/GHz):	-0.1x √f

IV. MECHANICAL PROPERTIES

Center Cont.:	Captive
Outer Cont.:	Crimp
Coupling Nut Torque (N.m):	1.1
Cbl-Connector Retention Force (N):	200
Durability (cycles):	500



Shrink Tube (3/8"x1.0" 3:1)



RECOMMENDED CABLE STRIPPING DIM'S
Connector adds: 12,2 mm

Compatible with Standard: IEC 60169-15

MATL:		UNLESS OTHERWISE SPECIFIED				DFTM. Monica		TIMES MICROWAVE SYSTEMS An Amphenol Company				
		ALL DIMENSIONS ARE IN mm MACHINED SURFACES FINISH 1.6 RMS MAX. REMOVE ALL BURRS 0.15X45° MAX. BREAK MACHINE CORNERS 0.15X45° D MAX. FILLET R. TOLERANCES ON DECIMALS .X ±0.3 .XX ±0.15 ANGLES ±2° FRACTIONS ± N/A				DATE 2018.08.03						
USED ON: O						CHKD Patrick		EZ-200-SM-X SMA Male(Plug) Straight Non-Solder Pin No Braid Trim Connector for LMR-200 Cable				
						DATE 2018.08.03						
						APPD Joslen						
SCALE: N/A	DWG SIZE A4	DO NOT SCALE DRAWING		CODE IDENT	68999	DATE 2018.08.03		S H T	1 OF 1	3190-6434	R E V	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[EZ-200-SM-X](#)