


THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE SAME AS SHEET 1

REV	DESCRIPTION	DATE	BY
A	INITIAL RELEASE	10/28/22	YA



Dwg. Number	Customer P/N	Times P/N	Length(L) in 'inch'
IE-00417-01	-	IBPS092-SMPMF SMPMF-4.0IN	4 +0.20/-0
IE-00417-02	-	IBPS092-SMPMF SMPMF-6.0IN	6 +0.20/-0
IE-00417-03	-	IBPS092-SMPMF SMPMF-8.0IN	8 +0.20/-0
IE-00417-04	-	IBPS092-SMPMF SMPMF-10.0IN	10 +0.20/-0
IE-00417-05	-	IBPS092-SMPMF SMPMF-12.0IN	12 +0.24/-0

1.0 Scope

This drawing documents the construction and performance of PT- 092 cable assemblies manufactured by Times Microwave systems.

2.0 Cable Information

- 2.1 Cable to be PT-092
- 2.2 Jacket color to be Black
- 2.3 Jacket material to be Tefzel
- 2.4 Nominal cable impedance to be 50 ohms
- 2.5 Cable diameter to be 0.101" [2.57mm] (Nominal).

3.0 Connector Information

- 3.1 Forward Connector
Type Mini SMP (F) Straight Connector (SP129)
- 3.2 After Connector
Type Mini SMP (F) Straight Connector (SP129)

Unless otherwise specified, dimensions are in INCH. Tolerances are applicable when specified.

These drawings and specifications contain proprietary information which is the property of Times Microwave Systems.

Approvals

Drawn YA 10/28/22

Checked

Approved



TIMES MICROWAVE SYSTEMS

www.timesmicrowave.com

PT-092 CABLE ASSEMBLY
(Space Assemblies)

Size A CAGE CODE 68999 Drawing No.: IE-00417-XX

Scale: NA

Rev. (A)

Sheet: 1 of 3

THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE SAME AS SHEET 1

REV	DESCRIPTION	DATE	BY
A	INITIAL RELEASE	10/28/22	YA

4.0 Electrical Performance

4.1 Frequency range: DC – 40GHz

4.2 Insertion loss & VSWR: As per below table,

Dwg. Number	Max. Insertion Loss in dB	Max. VSWR
	@ 40GHz	@ 40GHz
IE-00417-01	1.04	1.40
IE-00417-02	1.34	1.40
IE-00417-03	1.63	1.40
IE-00417-04	1.93	1.40
IE-00417-05	2.23	1.40

5.0 Mechanical Performance

5.1 Overall Length to be specified length.

5.2 Minimum Bend radius is 0.437" [11.1mm].

6.0 Environmental Performance

6.1 Installation Temperature Range (-65°C to +150°C)

6.2 Storage Temperature Range (-65°C to +150°C)

6.3 Operating Temperature Range (-65°C to +150°C)

7.0 Marking

7.1 Markers are to be black text on White Color Marker Sleeve.

7.2 Marker Configuration to be:

Dwg. Number	Marker 1
IE-00417-01	Times Microwave Systems IBPS092-SMPMF SMPMF-4.0IN \$\$\$\$\$
IE-00417-02	Times Microwave Systems IBPS092-SMPMF SMPMF-6.0IN \$\$\$\$\$
IE-00417-03	Times Microwave Systems IBPS092-SMPMF SMPMF-8.0IN \$\$\$\$\$

Unless otherwise specified, dimensions are in INCH. Tolerances are applicable when specified.

These drawings and specifications contain proprietary information which is the property of Times Microwave Systems.

Approvals

Drawn	YA	10/28/22
Checked		
Approved		



TIMES MICROWAVE SYSTEMS

www.timesmicrowave.com

PT-092 CABLE ASSEMBLY
(Space Assemblies)

Size A	CAGE CODE 68999	Drawing No.: IE-00417-XX
-----------	---------------------------	-----------------------------

Scale: NA

Rev. (A)

Sheet: 2 of 3

THE REVISION STATUS OF ALL SHEETS OF THIS DRAWING IS THE SAME AS SHEET 1

REV	DESCRIPTION	DATE	BY
A	INITIAL RELEASE	10/28/22	YA

IE-00417-04	Times Microwave Systems IBPS092-SMPMFSPMPF-10.0IN \$\$\$\$\$
IE-00417-05	Times Microwave Systems IBPS092-SMPMFSPMPF-12.0IN \$\$\$\$\$

7.3 \$\$\$\$\$ = 5-digit Serial Number for this specific configuration.

7.4 Register to be Maintained for Serial Number.

8.0 NOTES

- 8.1 All Dimensions are in INCH.
8.2 Assemblies built in Class 100,000 clean room.
8.3 Low outgassing materials per ASTM E595.
8.4 Unless Otherwise Specified: Tolerance will be,

Linear Dimension	Tolerance
<20 INCH	±0.4 INCH
20-79 INCH	±0.6 INCH
>79 INCH	±0.8 INCH

****Tolerances are not accumulative.**

Unless otherwise specified, dimensions are in INCH. Tolerances are applicable when specified.

These drawings and specifications contain proprietary information which is the property of Times Microwave Systems.

Approvals

Drawn YA 10/28/22

Checked

Approved



TIMES MICROWAVE SYSTEMS

www.timesmicrowave.com

PT-092 CABLE ASSEMBLY
(Space Assemblies)

Size
A

CAGE CODE
68999

Drawing No.:
IE-00417-XX

Scale: NA

Rev. (A)

Sheet: 3 of 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[IBPS092-SMPMFRASMPMFRA-10.0IN](#) [IBPS092-SMPMFRASMPMFRA-12.0IN](#) [IBPS092-SMPMFRASMPMFRA-4.0IN](#) [IBPS092-SMPMFRASMPMFRA-6.0IN](#) [IBPS092-SMPMFRASMPMFRA-8.0IN](#)