

NOTES:

1) LABEL REQUIREMENT:


- LABELS ARE M23053/5 ,WHITE. ACCEPTABLE SUBSTITUTION IS DAT-38-292 OR TRANSVINYL (DAT-63-292-2.5).
- LOCATE APPROXIMATELY AS SHOWN.

2) TEST REQUIREMENT:

IL @ 1310 nm SHALL BE 3.25 dB MAX.

REVISION HISTORY – ALL SHEETS ARE AT THE SAME REVISION

REV	DESCRIPTION	DATE	APPROVED
-	INITIAL RELEASE	2017/11/13	



5	AFSI-PRE T BOX	BOX, SMALL FIBER CABLE 10X10X2 W/AFSI GRAPHICS	1
4	BSFT0600	FURCATION TUBE, 2MM ID600UM, BLACK	2 FEET
3	WTTO-0400	CABLE,4 FIBER 9/125 TACTICAL DISTRIBUTION	3.61 FEET
2	BFCC2000-BL-1	FC SM CONNECTOR, METAL BODY W/CERAMIC FERRULE; BLUE BOOT	4
1	EB4H8280-344A3	4 CH JAM NUT RECEPT,INT MOUNT,SHORT TAC, BLACK ALUM,1310/1550	1
ITEM NO.	PART NO.	DESCRIPTION	QTY/ LENGTH

MATERIAL:

DFTR/Designer:
C. Hoang 2017/10/20
Check By:
B. Waite 2017/10/24
Manufacturing:
B. Waite 2017/10/24
Market Manager/PLM:
Q. Abraham 2017/10/25
Configuration Management:
L. Brown 2017/11/13

DRILLED HOLE DIAMETER TOLERANCE
Ø.000 TO Ø.125 $\pm .001$ Ø.251 TO Ø.500 $\pm .002$
Ø.126 TO Ø.250 $\pm .005$ Ø.501 TO Ø.750 $\pm .008$

DO NOT SCALE DRAWING
UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOL ON ANGLES 43°
1 PL ±.1 2 PL ±.02 3 PL ±.010
INTERPRET DIM AND TOL PER
ASME 14.5M-1994

This Document contains proprietary information and such information is prohibited from disclosure to others, publication or duplication in whole or in part without written permission from Amphenol Fiber Systems International.
Copyright © 2017 Amphenol Fiber Systems International.
Non published work. All rights reserved.

Amphenol FSI

TITLE:

4 CHANNEL TACBEAM JAM NUT RECEPTACLE TO FC ASSEMBLY, SM

SIZE	CAGE CODE	DWG NO	REV
A	OYPM2	2016040801TD-D1	-
SCALE: NONE			SHEET 1 OF 1

J1	PINOUT DIAGRAM	B LABEL INFORMATION
A1	● ——— ●	A1
B1	● ——— ●	B1
A2	● ——— ●	A2
B2	● ——— ●	B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[2016040801TD-D1](#)