



REV	ECN	DESCRIPTION	DATE	MODIFIED
1		PRE-RELEASE	Aug-04-2022	

Amphenol PCD SZ
ORIGINAL
PDF Format
R&D



安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受 控 文 件


2022年8月26日

HVCOCF0212DNL XXXX


LENGTH	TOLERANCE
0~1000mm	+25 -10
1001~5000mm	+40 -10
>5000mm	+50 -20

DIMENSIONS		TOLERANCES		PROJECTION	TITLE						
ANSI Y14.5M		.X ± 0.5			CCS2 Vehicle INLET						
UNITS: MM		.XX ± 0.05			DC1000V/500A; 3 PHASES AC480V/63A						
CAD FILE		ANGLES ± 2.0°			Cable Assembly						
					Aug-04-2022						
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF Amphenol PCD Shenzhen Co. Ltd Amphenol PCD Shenzhen Co. Ltd RESERVES THE RIGHT TO CLARIFY THIS DRAWING				CHKD		SIZE		DWG NO.		REV
							A3		C-HVCOCF0212DNLXXXX		1
					APPD		CODE: 58982		SCALE 1:1		SHEET 1 OF 2

WIRE DIAGRAM FOR LED INDICATOR LIGHT



CABLE CONNECT METHOD



安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受 控 文 件

2022年8月26日

*Notes:

1.Cable assembly data:

★ Rated Voltage and Current:

1000V DC / 500A Max(DC+,DC-); When the charging current is more than 300A ,
Recommend to use the charging gun with Liquid-cooled system

480V AC / 63A Max(L1,L2,L3,N);

30 V DC / 2A Max (CP,PP);

★ Insulation Resistance:100MΩ Min/DC1000V(DC+&DC-&PE&AC)

100MΩ Min/DC500V(PP&CP)

★ Dielectric Withstand Voltage:3000V/AC r.m.s/ DC+,DC-,PE

2000V/AC r.m.s/ L1,L2,L3,N

500V/AC r.m.s/ PP,CP

★ IP-Class: IP44(Mated)

IP55(With LIDS)

IP67(Connector Enclosure Tail)

◎Durability:10000 cycles.

★ RoHS Compliance;

Ambient Temperature: -30℃ ~ +50℃.

2.Connector reference: C-HVCOCF02XDN

3.Reference IEC 62196-3;

⑬	P05Z000089	PA WAVE PIPE BLACK 8.5*11.5mm	AR	m
⑮	C210003609	CABLE TIE BLACK 2.5X100mm	1	EA
⑭	P01BS00025	SIGNAL TERMINAL: P01BS00025 FOR 0.5-0.75mm²	9	EA
⑬	LVRC10CF020D	SIGNAL CONNECTOR: LVRC10CF020D 10POS	1	EA
⑫	C2100054201	SINGLE-WALL H.S.T: Ø12mm BLACK	0.10	m
⑪	P05B000022	SINGLE-WALL H.S.T: Ø30mm BLACK	0.08	m
⑩	C210006837	SINGLE-WALL H.S.T: Ø3.2mm WHITE	0.15	m
⑨	C210006511	SINGLE-WALL H.S.T: Ø12mm WHITE	0.10	m
⑧	C210004342	SINGLE-WALL H.S.T: Ø30mm WHITE	0.06	m
⑦	P01BC00159	1C*0.75mm²,XLPE,OD1.8±0.1mm,GREEN/GREY	AR	m
⑥	P01BC00187	1C*0.75mm²,XLPE,OD1.8±0.1mm,RED	AR	m
⑤	P01BC00186	1C*0.75mm²,XLPE,OD1.8±0.1mm,BLACK	AR	m
④	P01BC00153	16mm² SHIELDING, ORANGE, ID:6.95±0.20, OD:9.90±0.3	AR	m
③	P01BC00036	25mm² UNSHIELDING, YELLOW/GREEN, OD:9.6±0.2	AR	m
②	P01BC00154	150mm² SHIELDING, ORANGE, ID:20.6±0.5, OD:24.9±0.5	AR	m
①	HVCOCF0212DN	VEHICLE INLET: HVCOCF0212DN DC 500A, AC 63A, WITH CAP	1	EA
ITEM	P/N	DESCRIPTION	QTY	UNIT

SIZE

DWG NO.

REV

A3

C-HVCOCF0212DNLXXXX

1

CODE: 58982

SCALE

1:1

SHEET

2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[HVCOCF0212DNL3000](#)