

PART NUMBER

10-101982-8
-10
-12

-14
-16
-18

-20
-22
-24

APPROX AREA SQ. IN.	THREAD- CLASS 2B
2.5319	.4375-28 UNEF
3.1216	.5625-24 UNEF
3.7191	.6875-24 UNEF
4.2723	.8125-20 UNEF
5.3516	.9375-20 UNEF
5.7952	1.0625-18 UNEF
7.7968	1.1875-18 UNEF
8.6301	1.3125-18 UNEF
8.9974	1.4375-18 UNEF

REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
A3	REDRAWN, SAME SIZE; STANDARDIZED, ADD & REL -XXE, -XXG ECN: 54525-346	SHEPLER 4-27-73	<i>James</i>
B	(CL II) SEE REV NOTICE ECN: 21391-3	12/20/88 SHEIRER	<i>Wesley</i>
C	(CLII) ADDED NOTE 4 & FLAG 4 ECN: 23672	2-14-90 DEMATED	<i>Shepler</i> <i>Z. Kipp</i>
D	(CLII) SEE CHANGE NOTICE ECN: 29140	12-9-94 DEMATED	<i>JED</i>
E	(CLII) ADD REL -XXV FINISH DATA ECN: 80672	9-7-95 DEMATED	<i>JED</i>

FINISH DATA

FINISH SPEC	PART NO. SUFFIX	MADE FROM SUFFIX
CHROMATE TREAT	9-3350	-XX0
BRIGHT CADMIUM PLATE	9-2158	-XX1
BLACK ANODIZE	9-3487	-XX2
OLIVE DRAB CADMIUM PLATE	9-3047	-XX3
GREY ANODIZE	9-3487	-XX4
ANODIC COATING	9-3290	-XX5
NOT AVAILABLE		
BRIGHT CADMIUM PLATE NICKEL BASE PLATE	9-4332	-XX7
BRIGHT NICKEL	9-3435	-XX8
OLIVE DRAB CADMIUM PLATE, NICKEL BASE PLATE	9-4960	-XX9
CHROMIUM PLATE	9-6002	-XXE
NICKEL ALLOY PLATE	9-6914	-XXG
BLACK ZINC ALLOY PLATE	9-9181	-XXY
GREEN ZINC ALLOY PLATE	9-9263	-XXU
BLACK ZINC ALLOY CONDUCTIVE PLATE	9-9181-1	-XXX
		10-101982-()B OR 10-101982-()C

4. 10-101982-()C MADE FROM NOT APPLICABLE FOR SIZES 20, 22 & 24.

3. FOR RELEASE STATUS OF DESIRED PART, SEE SEPARATE PARTS LIST.
2. THREADS TO BE CLASS 2B AND IN ACCORDANCE WITH FEDERAL HANDBOOK H-28.
1. TO COMPLETE PART NUMBER AND MADE FROM, SEE FINISH DATA, ADD APPLICABLE LAST CHARACTER FOR DESIRED FINISH AND PERMISSIBLE MADE FROM PART. FOR RELEASE STATUS AND TO DETERMINE A SPECIFIC "MADE FROM" PART, SEE SEPARATE PARTS LIST.

F	ADD & RELEASE - XXU PLATING ECN: 81213	1-22-96	<i>RJB</i>
G	ADD & RELEASE - XXX PLATING ECN: 85416	9-16-98	<i>JED</i>

NOTES:

10-101971 & OTHERS
NEXT ASSEMBLY

SEE NOTE 1

FIND NO.	QTY REQD	CODE IDENT	PART NUMBER	DESCRIPTION	NOTE REF
PARTS LIST					
USE OF THIS DOCUMENT IS UNLIMITED. DOCUMENTS REFERENCED HEREON CONTAIN LIMITED RIGHTS DATA.					
UNLESS OTHERWISE SPECIFIED LINEAR DIMENSIONS ARE IN INCHES TOLERANCES: .XXX ± .010 .XX ± .03 .X ± .1 ANGLES ± 2° OTHER STANDARDS PER 9-3800 AND MIL-D-1000. NOTE REF		SIGNATURES PREPARED SCHOFIELD CHECKED B. Jones MATERIAL SPEC MATERIAL APPROVED E. Shepler PROCESS SPEC APPROVED Jameson		DATES 2-14-57 6-11-73 4-27-73 6/11/73	
The Bendix Corporation Electrical Components Division Sidney, New York				NUT, CABLE CLAMP, STRAIN RELIEF, TYPE PC()	
SIZE B		CODE IDENT NO. 77820		10-101982	
SCALE NONE		WT PL		SHEET	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[10-101982-083](#) [10-101982-103](#) [10-101982-123](#) [10-101982-12G](#) [10-101982-143](#) [10-101982-163](#) [10-101982-183](#)
[10-101982-203](#) [10-101982-223](#) [10-101982-243](#) [10-101982-20X](#)