


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 46875	07/22	SEE PDM



MATERIAL:

CONNECTORS: SMP R/A FEMALE (1222-40094)  
SMA MALE (SF2911-60966)



CABLE: Ø.047 SUPERFLEX CABLE

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS  
FREQ. RANGE: DC TO 26.5 GHz.

SV P/N	OAL
7012-2006	3.000"
7012-2007	6.000"

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		<div> www.svmicrowave.com</div> <div>TITLE: SMP FEMALE R/A TO SMA MALE CABLE ASSEMBLY FOR .047 SUPERFLEX CABLE</div>	
FINISH:	SEE NOTES	FRACTIONAL: ±1/64    ANGULAR: X° ±1°0'    X°X' ±15'		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA. 'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS			
SURFACE AREA: N/A		DECIMAL: .X    ±.030 .XX    ±.010 .XXX ±.005				SIZE DWG. NO. 7012-2006-2007	
PROPRIETARY		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		THIRD ANGLE PROJECTION		DRAWN: KRR 07/21/22	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.				CHECKED: SEE PDM		SCALE: 4:1	
				APPROVED: SEE PDM			
						SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7012-2006](#)