












1. MATERIAL:
CONTACTS: COPPY ALLOY
SHELL: COPPY ALLOY
HOUSING: UL 94V-0 RATED THERMOPLASTIC
2. PLATING:
SEE PRODUCT NUMBER CODE
3. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
4. RECOMMENDED PC BOARD THICKNESS OF 1.57mm
5. 2.67mm MAXIMUM PANEL THICKNESS IF MOUNTED BEHIND PANEL
6. CONTACT PLATING CODE OPTION 1 DOES NOT MEET THE PLATING SPECIFIED PER UNIVERSAL SERIAL BUS SPECIFICATION REVISION 1.0
7. MAXIMUM PANEL THICKNESS TO BE 2.67mm IF MOUNTED BEHIND PANEL.
8. TORQUE SPEC 2.0kgf-cm MAX.



www.fciconnect.com		Surface  Tolerance Std		projection 		MM 	
TOLERANCES UNLESS OTHERWISE SPECIFIED		ANGULAR		size		Scale	
Dr	PETER	0.X		A4		1 : 1	
Eng	R Y LIU	0.XX		±0.2			
Chr	R Y LIU	0.XXX		±		ECN ELX-NH5753	
Appr	JENN TSAO	Product family		Spec ref			
FCI 		USB REVERSED		dwg no		Rev.	
++ RECEPTACLE SMT				74626		S	
catalog no				CUSTOMER		sheet 1 of 3	



Copyright FCI.



P.C. BOARD LAYOUT FOR 5 PIN 74626-X01XB

www.fciconnect.com				surface	tolerance	std	projection	MM
Dr	PETER	7/8/98	ANGULAR	TOLERANCES UNLESS OTHERWISE SPECIFIED				size
Eng	R Y LIU	7/8/98	LINEAR	0.X	±0.3	±0.2	A4	Scale
Chr	R Y LIU	7/8/98	0° ±5°	0.XX	±	±	ECN	1:1
Appr	JENN TSAO	7/8/98	Product family	0.XXX	±	±	ELX-N15753	Rev.
USB REVERSED				Spec ref				S
RECEPTACLE SMT				CUSTOMER				74626
catalog no				sheet 2 of 3				

1

2

3

4

PRODUCT NUMBER CODE

A
74626 - X X X X P LF

BASE PRODUCT NUMBER

HOUSING COLOR OPTIONS

- 0 - WHITE
 - 1 - BLACK
 - 2 - WHITE + SHELL NICKEL PLATING ONLY
- SENSOR CONTACT OPTION

- 0 - WITH SENSOR CONTACT
- 1 - WITHOUT SENSOR CONTACT

SHELL OPTIONS

- 1 - WITHOUT BACK SHIELD
 - 3 - WITHOUT BACK SHIELD & NICKEL PLATING ONLY
 - S - WITHOUT BACK SHIELD & NICKEL PLATING ONLY (SPECIAL MATERIAL FOR DURABILITY 12,000 CYCLES)
- TERMINAL PLATING OPTION

- 0 - 1.25um Ni UNDERPLATE
- 0.76um GXT CONTACT AREA
- 2.50 um TIN/LEAD TAIL AREA

PACKAGING OPTION

- B - TUBES
- R - TAPE & REEL


DATE CODE

LEAD FREE




Copyright FCI.

D



STYLE 1



STYLE 2

NOTES :

1. P/N'S WITH SUFFIX "LF" ARE LEAD FREE P/N'S
2. PACKING STANDARD GS-14-920 WILL BE APPLIED FOR LEAD FREE P/N'S
3. FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008
4. FOR LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 40 SECONDS IN A CONVECTION, INFRARED OR VAPOR PHASE REFLOW OVEN.
5. AVAILABLE P/N'S NOW IN FCI ARE

PART NUMBER	STYLE
74626-0010XXLF	STYLE 1
74626-1010XXLF	STYLE 1
74626-0110XXLF	STYLE 1
74626-1130XXLF	STYLE 1
74626-2010XXLF	STYLE 2
74626-2110XXLF	STYLE 2
74626-1110XXLF	STYLE 1
74626-01S0XPFL	STYLE 2
74626-11S0XPFL	STYLE 2

www.fciconnect.com		surface		tolerance std		projection		MM	
TOLERANCES UNLESS OTHERWISE SPECIFIED		✓							
Dr	PETER	7/8/98	ANGULAR	0.X	±0.3	size	A4	Scale	1:1
Eng	R Y LIU	7/8/98	LINEAR	0.XX	±0.2	ECN	ELX-N15753	Rev.	S
Chr	R Y LIU	7/8/98	0° ±5°	0.XXX	±	Spec ref			
Appr	JENN TSAO	7/8/98	Product family						
USB REVERSED		RECEPTACLE SMT		74626		CUSTOMER		sheet 3 of 3	
FCI logo		catalog no							

1

2

3

4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[74626-0110BLF](#) [74626-0010BLF](#) [74626-11S0BPLF](#) [74626-11S0RPLF](#) [74626-01S0RPLF](#)