



1. MATERIALS AND FINISHES:
BODY - BRASS, NICKEL PLATING
CONTACT - BRASS, GOLD PLATING
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 31-2367, AND DATE CODE"
C. FERRULE & CONTACT ARE SHIPPED LOOSE
5. SHOWS CABLE ENTRY DIMENSIONS.
6. CUSTOMER NOTE: SOLDER CONTACT TO CABLE.
WHEN CRIMPING CONTACT TO CABLE, CRIMP WITH
AND DIE SET 227-1221-11, CAVITY 'B' (M2250/5-11)
7. CRIMP WITH AMPHENOL TOOL 227-944 (M2250/5-11)
SET 227-1221-11, CAVITY 'A' (M2250/5-11)

REVISIONS


REV	DESCRIPTION	DATE	ECO	APPR
	RELEASE TO MFG.			
V	ADDED COD; STAMP "AMPHENOL" WAS "74868"\RD-DM12092001R3	19-Oct-12	49079	S.H
W	REMOVE 'M23329/4-01-03', 'MIL-CRIMP 23329 IN TITLE' \RD-DM14090501J9	17-Sep-14	50170	S.H



RECOMMENDED CABLE STRIPPING DIMENSIONS



SCALE 2.000



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1°	MATERIAL -	DRAWN JONA	DATE 09-Sep-14	TITLE TNC PLUG FOR RG58 & 141/U CABLE		Amphenol RF www.amphenolrf.com	
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.		ENGINEER S.LI	DATE 13-Aug-12			DRAWING NO. 31-2367	
	REFERENCE EAR # 961603 AND	APPROVED S.HSIEH	DATE 09-Sep-14	SCALE: 4.0:1.0	SHEET 2 OF 2	ITEM NO. 31-2367	
	CONFIGURATION LEVEL: <input type="checkbox"/> <input type="checkbox"/> <input type="checkbox"/>	CAD FILE	DWG SIZE B		REV W	PART NO. 31-2367	
	FINISH						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[31-2367](#) [031-2367](#)