

5

4

3

2

1

NOTES:

1. MATERIALS AND FINISHES:
SMA STR PLUG - BRASS, GOLD PLATING


AMC RA PLUG:
HOUSING - PBT, BLACK
CONTACT & GROUND CONTACT - PHOSPHOR BRONZE, GOLD PLATING

CABLE - 1.13 MM CABLE


2. ELECTRICAL:
A. IMPEDANCE: 50 OHM

3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-902-544-XXX AND DATE CODE"

SCALE 1.000



LENGTH 'L' (SEE TABLE)



LENGTH TABLE

PART NUMBER (IMPERIAL)	LENGTH AND TOLERANCE 'L' IN MM (INCHES)
95-902-544-050	50.00 ± 3.81 [1.969 ± 0.150]
95-902-544-100	100.00 ± 3.81 [3.937 ± 0.150]
95-902-544-150	150.00 ± 3.81 [5.906 ± 0.150]
95-902-544-200	200.00 ± 5.08 [7.874 ± 0.200]
95-902-544-250	250.00 ± 5.08 [9.843 ± 0.200]
95-902-544-300	300.00 ± 5.08 [11.811 ± 0.200]

DESIGN REQUIREMENTS:

☒ FREQUENCY: DC - 6 GHz

☒ CONTINUITY

☐ VSWR: ____ MAX.

☒ HI-POT: 200 VRMS

☐ INS. LOSS: ____ dB MAX.

☐ OTHER:

Amphenol RF

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

THIRD ANGLE PROJ.

REFERENCE

ENG# 10472

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE:
<0.5mm = ±0.05mm [$<0.020 = \pm 0.002$]
>0.5 - 6mm = ±0.1mm [$>0.020 - 0.236 = \pm 0.004$]
>6.00 - 30mm = ±0.2mm [$>0.236 - 1.181 = \pm 0.008$]
>30.00 - 120mm = ±0.3mm [$>1.181 - 4.725 = \pm 0.012$]

ANGLES = ±1°

SEE NOTES

ENGR.1 VIJAY N M ENGR.2 DATE 02-FEB-21

TITLE SMA STR PLUG TO AMC RA PLUG USING 1.13 MM CABLE VARIOUS LENGTH

SHEET NO. 2 OF 2 SCALE: 5.0:1.0

SIZE B

DRAWING NO. 95-902-544-XXX

ITEM NO. 95-902-544-XXX

PART NO. 95-902-544-XXX

REV B

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[095-902-544-050](#) [095-902-544-100](#) [095-902-544-150](#) [095-902-544-200](#) [095-902-544-250](#) [095-902-544-300](#)