



REVISIONS				
REV	DESCRIPTION	DATE	ECN	APPR
A	RELEASE TO MFG.	22-Jun-20	15223	S.HSIEH



- Notes:
- 1.10 sprocket hole pitch cumulative tolerance $\pm 0.20\text{mm}$
(每10个链轮齿孔直径累计公差为 $\pm 0.2\text{mm}$)
 2. Carrier camber not to exceed 1mm in 250mm.
(传送料带弯曲变形度每250MM不超过1MM)
 3. A and B measured on a plane 0.3mm above the bottom of the pocket. (A0与B0在同一平面测量且距口袋底部0.3MM)
 4. K measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
(K0为口袋底部与材料表面的平面距离。)
 5. All dimensions meet EIA-481-D requirements.
(所有尺寸符合EIA-481-D标准要求。)
 6. Material: Black Antistatic polystyrene.
(材料:黑色防静电聚苯乙烯。)
 7. Thickness: $0.50 \pm 0.05\text{ mm}$.
(厚度: $0.50 \pm 0.05\text{毫米}$ 。)
 8. Packing length per 13" reel : 8.16Meters.
(每个13"卷轴包装长度为8.16米。)
 9. Component loader per 13" reel : 600 pcs.
(每个13"卷轴可装600个零件。)

技术要求:
在没有保护膜的情况下, 0-90度往返折弯3次, 卷带不会破裂; 冷封带0.3~1.3N; 厚度及防静电要求需满足要求, 防静电性能使用寿命至少大于半年。载带侧壁支撑力2kgf以上。

ITEM	W	A ₀	B ₀	K ₀	K ₁	P ₁	F	E	D ₀	D ₁	P ₀	P ₂	T
DIM	24±0.3	6.36±0.1	6.36±0.1	7.29±0.1		12.0±0.1	11.5±0.1	1.75±0.1	1.5 ^{+0.1} / _{-0.00}		4.0±0.1	2.0±0.1	0.5±0.05

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

THIRD ANGLE PROJ.	REFERENCE SMP-MSSB-PCT-5	EAR# 9913	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC (INCHES) AND TOLERANCES ARE: <0.5mm = $\pm 0.05\text{mm}$ [$-0.020 = \pm 0.002$] >0.5 - 6mm = $\pm 0.1\text{mm}$ [$>0.020 - 0.236 = \pm 0.004$] >6.00 - 30mm = $\pm 0.2\text{mm}$ [$>0.236 - 1.181 = \pm 0.008$] >30.00 - 120mm = $\pm 0.3\text{mm}$ [$>1.181 - 4.725 = \pm 0.012$] ANGLES = $\pm 1^\circ$	MATERIAL	TITLE SMP JACK, PIN CONTACT PCB RECEPTACLE SMOOTH BORE TAPE AND REEL PACKED	DRAWING NO. SMP-MSSB-PCT-5T ITEM NO. SMP-MSSB-PCT-5T PART NO. SMP-MSSB-PCT-5T	REV A	
	DATE 17-Jun-20			ENGINEER E.W.U	SHEET NO. 3 OF 3			SCALE: 10.0:1.0
	Amphenol RF SIZE B TITLE							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SMP-MSSB-PCT-5T](#)