



|                |             |                      |  |                  |          |  |  |
|----------------|-------------|----------------------|--|------------------|----------|--|--|
| ROHS COMPLIANT |             | PRODUCT DATA DRAWING |  | REVISION HISTORY |          |  |  |
| REV            | DESCRIPTION |                      |  | DATE             | APPROVED |  |  |
| A              | DCN 41650   |                      |  | 09/15            | DAL      |  |  |
|                |             |                      |  |                  |          |  |  |



2X .312[ 7.92 ]  
HEX.

3X Ø.020±.001[ 0.51±0.03 ]

1.030[ 26.16 ] MAX.



MATERIAL:

BODY & COUPLING NUT:

LOCK RING & CONTACT:

INSULATOR:

GASKET:

SHRINK TUBING:

CRIMP RING:

STAINLESS STEEL PER AMS-5640,  
ALLOY UNS S30300, TYPE 1

BERYLLIUM COPPER PER ASTM B196,  
ALLOY No. UNS C17300, TD04

PTFE PER ASTM D1710, TYPE I, GRADE 1, CLASS B

SILICONE RUBBER PER A-A-59588,  
CLASS 2B, GRADE 50/60

MIL-DTL-23053/4

COPPER PER ASTM B 301, ALLOY UNS C18700, H04

FINISH:

COUPLING NUT:

BODY, CONTACT & CRIMP RING:

PASSIVATED PER AMS-2700

GOLD PER ASTM B 488, TYPE II,  
CODE C, CLASS 1.27, OVER NICKEL  
PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

PERFORMANCE:

IMPEDANCE:

50 OHMS

|           |           |   |
|-----------|-----------|---|
| MATERIAL: | SEE NOTES | DIMENSIONS ARE IN INCHES TOLERANCES:<br>FRACTIONAL: ±1/64    ANGULAR: X°    ±1°0'<br> |
|-----------|-----------|---|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[M39012/55-3009](#)