




REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
K	PRODUCT DRAWING (EAR13732)	JUN16/10	K.L.

ORDERING CODE: F C C 1 7 - E 0 9 P M - 4 4 0 G

SERIES

SIZE/NUMBER OF CONTACTS
E09, A15, B25, OR C37

CONNECTOR STYLE

P = PIN
S = SOCKET

TERMINATION TYPE

M = SOLDER CUP

MOUNTING

2 = .120[3.05] DIA THROUGH HOLE
3 = #4-40 UNC SELF-LOCKING THREAD
4 = #4-40 UNC THREAD
6 = M3 x 0.5 THREAD
E = CODE 4 MOUNTING WITH #4-40 UNC
HEX JACK SOCKET SUPPLIED LOOSE

CONTACT FINISH/GOLD THICKNESS
NO DIGIT = STANDARD 15 MICROINCHES
[0.38 MICRONS] GOLD
G = 50 MICROINCHES [1.27 MICRONS]
GOLD
MODIFIER
0 = STANDARD
FILTER CAPACITANCE
D = 50 pF 5 = 1000 pF
B = 100 pF 7 = 1200 pF
0 = 180 pF 6 = 1300 pF
T = 220 pF J = 1500 pF
F = 330 pF E = 2200 pF
L = 380 pF 9 = 5600 pF
1 = 470 pF 8 = 47000pF
4 = 820 pF N = NO FILTERS
REFER TO AMPHENOL
CATALOGUE FOR FILTER
PERFORMANCE CHARACTERISTICS

NOTES:

- MATERIALS: - SHELLS - TIN PLATED STEEL
- CONTACTS - PHOSPHOR BRONZE
PLATED WITH GOLD OVER NICKEL
ON THE MATING AREA AND
TIN-LEAD ON THE TERMINALS
- INSULATOR - ENGINEERING
THERMOPLASTIC, FLAMMABILITY
RATING UL94V-0, BLACK.
- CONTACT RESISTANCE: 15 MILLIOHMS MAXIMUM.
- INSULATION RESISTANCE: 3000 MEGOHMS MINIMUM
- CURRENT RATING: 5 AMPS MAXIMUM
2 AMPS FILTERING MAXIMUM
- OPERATING TEMPERATURE: -40°C TO 85°C.
- TOLERANCE, UNLESS INDICATED OTHERWISE,
±.005 [0.13].

SIZE	STYLE	A±.015 [0.38]	B±.005 [0.13]	C±.005 [0.13]	D±.005 [0.13]	E BSC.
E09	PIN	1.213 [30.81]	-----	.666[16.92]	.984 [24.99]	.432 [10.97]
	SOCKET		.643[16.33]	-----		
A15	PIN	1.541 [39.14]	-----	.994[25.25]	1.312 [33.32]	.756 [19.20]
	SOCKET		.971[24.66]	-----		
B25	PIN	2.088 [53.04]	-----	1.534[38.96]	1.852 [47.04]	1.304 [33.12]
	SOCKET		1.511[38.38]	-----		
C37	PIN	2.729 [69.32]	-----	2.182[55.42]	2.500 [63.50]	1.956 [49.68]
	SOCKET		2.159[54.84]	-----		

.045
[1.14]
SOLDER CUP
END VIEW
ACCEPTS UP TO
20 AWG WIRE

DRAWN I.ESSAJEE	DATE 98/03/09
DESIGNED K.LAMBIE	98/03/04
CHECKED	
I. E. APPRD.	
Q. A. APPRD.	
DWG. APPRD.	
ENG. REL. NO.	
REF.	
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554

Amphenol Canada Corp.

TITLE
FCC17 FILTERED D-SUB
CONNECTOR, PIN & SOCKET,
SOLDER CUP CONTACTS

DWG C	DRAWING NO. P-FCC17-XXXXM-XXOX	REV. K
SCALE 3/1	WT. -----	SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[FCC17-E09PM-490](#) [FCC17-A15SM-240](#) [FCC17-A15SM-210](#) [FCC17-B25SM-290](#) [FCC17-B25SM-250](#) [FCC17-A15PM-210](#) [FCC17-A15PM-240](#) [FCC17-B25PM-240](#) [FCC17-E09SM-210](#) [FCC17-E09SM-240](#) [FCC17-E09SM-290](#) [FCC17-B25PM-210](#) [FCC17-B25PM-290](#) [FCC17-E09PM-240](#) [FCC17-E09PM-290](#) [FCC17-E09PM-210](#) [FCC17-E09PM-250](#) [FCC17-E09SM-490](#) [FCC17-E09PM-280](#) [FCC17-B25SM-240](#) [FCC17-A15SM-2B0](#) [FCC17-E09PM-450](#) [FCC17-A15PM-280](#) [FCC17-A15SM-280](#) [FCC17-A15SM-450](#) [FCC17-B25PM-280](#) [FCC17-C37PM-200](#) [FCC17-C37SM-280](#) [FCC17-E09SM-280](#)