





ROHS COMPLIANT		PRODUCT DATA DRAWING		REVISION HISTORY					
				REV	DESCRIPTION	DATE	APPROVED		
				-	DCN 39255	07/12	STW		
		3X .312[7.92] HEX.  .862[21.89]  1/4-36 UNS-2A  RECOMMENDED MOUNTING HOLE							
MATERIAL: BODY, INSERT, HEX NUT & CLAMP NUT: CONTACTS: FERRULE: BEAD: FINISH: BODY, INSERT, HEX NUT & CLAMP NUT: CONTACTS & FERRULE: PERFORMANCE: IMPEDANCE: FREQ. RANGE: VSWR: OPERATING TEMP.: STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1 BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04 BRASS PER ASTM B16, ALLOY UNS No. C36000 ULTEM 1000 PER ASTM D5205 PASSIVATED PER AMS-2700 GOLD PER ASTM B488, TYPE II, CODE C, CLASS 1.27, OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .00005" MIN. 50 OHMS DC TO 34.0 GHz 1.20:1 DC TO 34.0 GHz -55°C TO +125°C									
		MATERIAL: SEE NOTES		DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED			
		FINISH: SEE NOTES		FRACTIONAL: ± 1/64 ANGULAR: X° ± 1°0' X°X' ± 15'		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63+MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS			
		SURFACE AREA: N/A		DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005					
		THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994					
		THIRD ANGLE PROJECTION		DRAWN: NHR 07/30/12		TITLE: SVK BLKD JACK FOR Ø.141 S.R. CABLE			
				CHECKED: STW 07/30/12		SIZE B	CAGE CODE 95077		
				APPROVED: STW 07/30/12		DWG. NO.	SF1521-60044		
						SCALE: 6:1			
						SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SF1521-60044](#)