

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 44451	01/20	MKK

OAL ±.250
(SEE TABLE)

MATERIAL:

CONNECTORS:

CABLE:

SHRINK TUBING:

2.92mm MALE R/A (SF1512-60027)

SMPM FEMALE R/A (3222-40002)

T-FLEX 405

M23053/5

PERFORMANCE:

IMPEDANCE:

FREQ. RANGE:

50 OHMS

DC TO 18 GHz

SV P/N	OAL
7015-0998	6.000
7015-0999	12.000

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63+MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	<div>SVMICROWAVE www.svmicrowave.com</div> <div>TITLE: 2.92mm R/A MALE TO SMPM R/A FEMALE T-FLEX 405 CABLE ASSEMBLY</div> <div>SIZE DWG. NO. B 7015-0998-0999</div> <div>SCALE: 4:1</div> <div>SHEET 1 OF 1</div>
FINISH:	SEE NOTES	FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'		
SURFACE AREA:	N/A	DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005		
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		
THIRD ANGLE PROJECTION		DRAWN: SJ 01/22/20	CHECKED: MKK 1/29/20	APPROVED: MKK 1/29/20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[7015-0998](#)