


ELFP SERIES PART NUMBERING SCHEME

REV	ECN	APPD
-	3600	JEC 12/11/98
A	3865	JEC 11/9/99
B	4686	IQ 1/2/02
C	4761	IQ 2/20/02
D	4821	IQ 4/4/02
E	5742	2W 12/28/05



COLOR/PLATING
0=BLACK, TIN (STANDARD)
1=BLACK, SELECTIVE GOLD
G=GREEN, TIN
1G=GREEN, SEL. GOLD

MOUNTING EARS
0E=BLACK, TIN
1E=BLACK, SEL. GOLD
GE=GREEN, TIN
EG=GREEN, SEL. GOLD

CONSULT PCD FOR PART NO. AND
AVAILABILITY OF FOLLOWING OPTIONS:

- * CUSTOM COLORS
- * CUSTOM MARKING
- * CUSTOM KEYING
- * SELECTIVE CONTACT LOADING

RA
RATINGS
CURRENT - 15A
VOLTAGE - 300V
U.L. FILE NO. E83421

SA
RATINGS
CURRENT - 15A
VOLTAGE - 300V
CSA FILE NO. LR69703


DIN VDE 0627:1986
DIN VDE 0110-1:1989
EN 60947-1:1991
EN 60947-7-1:1992

CURRENT - 15A
VOLTAGE - 300 V
TUV FILE NO. 20396

INSTALLATION
RECOMMENDATIONS:
WIRE RANGE: AWG #14-26, STRANDED
OR SOLID; AWG #12 STRANDED
WIRE STRIP LENGTH: .310"
TIGHTENING TORQUE: 7 LB-IN.


MATERIALS:
HOUSING: PPO, UL 94 V-0
CONTACT: COPPER ALLOY, OPTIONAL FINISH
SCREW: STEEL, NICKEL FINISH
WIRE CLAMP: COPPER ALLOY, NICKEL FINISH
OPERATING TEMPERATURE RANGE:
-40°C-95°C

DIMENSIONS ANSI Y14.5M UNITS: INCHES ACAD FILE	TOLERANCES .XX ±.01 .XXX ±.005 ANGLES ±2°	PROJECTION 	Amphenol Pcd SPECIFICATION DRAWING	TITLE ELFP SERIES PLUGGABLE TERMINAL BLOCK, RIGHT ANGLE			
ENGR J. WILKINSON 11/8/98							
ORIGINAL STAMPED IN RED	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD INC. PEABODY, MA		CHKD A. PATRIE 12/4/98	SIZE A	DWG NO. ELFP02110		REV E
			APPD J. CAHALY 12/11/98				
			CODE: 58982 SCALE: NONE SHEET 1 OF 2				





WITHOUT MOUNTING EARS

L=NUM OF POS X CL SPACING





2X .097 (.197 CL)
.100 (.200 CL)



WITH MOUNTING EARS

L=NUM OF POS X CL SPACING



SIZE	DWG NO.	REV
A	ELFP02110	E
CODE: 58982	SCALE: NONE	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[ELFP07210](#) [ELFP11210](#) [ELFP05110](#) [ELFP02110](#)